

CP A BATTERY 24V DC17AH**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The 5 battery modules with capacities from 1,2 Ah to 17Ah can supply up to 40 A for 30 minutes or 1 A for 30 hours and are fully compatible with the DC UPS control units CP DC UPS 24V 20A/10A & CP DC UPS 24V 40A. And for sure, the DURAeco series is a flexible & ease of use solution in a cost-effective design.

General ordering data

Version	Battery
Order No.	1251110000
Type	CP A BATTERY 24V DC17AH
GTIN (EAN)	4050118043136
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2021-07-31
Alternative product	2789930000

CP A BATTERY 24V DC17AH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	160 mm	Depth (inches)	6.299 inch
Height	178 mm	Height (inches)	7.008 inch
Width	242 mm	Width (inches)	9.528 inch
Net weight	13,330 g		

Temperatures

Storage temperature	-15 °C...40 °C	Ambient temperature	0°...+40°C (Charging); -15° ...+50°C (Discharging)
Operating temperature	0 °C...40		

Operating interfaces and control inputs

Temperature probe	NTC 100 kΩ
-------------------	------------

Input

Charging current, max.	2.55 A	Nominal capacity	17 Ah
Rated input voltage	24 V DC		

Output

Buffer time 10A	81 min	Buffer time 20A	34.2 min
Buffer time 40A	13.5 min	Output current, max.	50 A
Overload and short circuit protection	2x25 A fuse	Parallel connection option	Yes
Protection against inverse voltage	Yes	Temperature probe	NTC 100 kΩ

General data

Max. perm. air humidity (operational)	5 %...95 % RH	Protection degree	IP20
Shock wall acc. to IEC 68227	30 g	Vibration DIN rail/wall in accordance with IEC 68-2-6	- / 0.7 g

Insulation coordination

Protection class	III, with no ground connection, for SELV
------------------	--

Connection data (input)

Conductor cross-section, AWG/kcmil , max.	6	Conductor cross-section, AWG/kcmil , min.	22
Conductor cross-section, flexible , min.	0.5 mm ²	Conductor cross-section, rigid , max.	16 mm ²
Conductor cross-section, rigid , min.	0.2 mm ²	Tightening torque, max.	1.5 Nm
Tightening torque, min.	1.2 Nm	Wire connection cross section, flexible (input), max.	16 mm ²

Connection data (output)

Conductor cross-section, AWG/kcmil , max.	6	Conductor cross-section, AWG/kcmil , min.	22
Conductor cross-section, flexible , max.	16 mm ²	Conductor cross-section, flexible , min.	0.5 mm ²
Conductor cross-section, rigid , max.	16 mm ²	Conductor cross-section, rigid , min.	0.2 mm ²
Number of terminals	2 (+ / -)	Tightening torque, max.	1.5 Nm
Tightening torque, min.	1.2 Nm		

Creation date May 5, 2024 8:55:21 AM CEST

CP A BATTERY 24V DC17AH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Connection data (signal)

Number of terminals	2	Wire connection cross-section, flexible (signal), max.	1.5 mm ²
Wire connection cross-section, flexible (signal), min.	0.2 mm ²	Wire connection method	Pluggable screw connection
Wire cross-section, AWG/kcmil, max.	16	Wire cross-section, AWG/kcmil, min.	28
Wire cross-section, solid, max.	1.5 mm ²	Wire cross-section, solid, min.	0.2 mm ²

Approbations

Certificate no. (cULus)	E349959	Institute (cULus)	CULUS
-------------------------	---------	-------------------	-------

Classifications

ETIM 6.0	EC002850	ETIM 7.0	EC002850
ETIM 8.0	EC002850	ETIM 9.0	EC002850
ECLASS 9.0	27-04-06-92	ECLASS 9.1	27-04-92-01
ECLASS 10.0	27-04-06-92	ECLASS 11.0	27-04-06-92
ECLASS 12.0	27-04-06-92	ECLASS 13.0	27-04-06-92

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	30bf869c-8adc-4ed2-ad02-c1fec963e943

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E349959

Downloads


Approval/Certificate/Document of Conformity	Declaration of Conformity
Engineering Data	CAD data – STEP
User Documentation	Operating instructions
Catalogues	Catalogues in PDF-format

CP A BATTERY 24V DC17AH

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Buffer Time

CP A BATTERY 24V DC17AH**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Slotted screwdriver**

VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Type	SDIS SL 1.0X5.5X125	Version
Order No.	1274680000	Screwdriver, Mounting tool
GTIN (EAN)	4050118073263	
Qty.	1 pc(s).	
Type	SDIS SL 0.6X3.5X100	Version
Order No.	1274660000	Screwdriver, Mounting tool
GTIN (EAN)	4050118072631	
Qty.	1 pc(s).	

W-Series

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type	WEW 35/2 V0 GF SW	Version
Order No.	1479000000	End bracket, Wemid, black, Rail: TS 35, when screwed in
GTIN (EAN)	4050118286779	
Qty.	50 pc(s).	
Type	WEW 35/1 V0 GF SW	Version
Order No.	1478990000	End bracket, Wemid, black, Rail: TS 35, when screwed in
GTIN (EAN)	4050118286892	
Qty.	50 pc(s).	