

KT 14**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

General ordering data

Version	Cutting tools, Cutting tool for one-hand operation
Order No.	1157820000
Type	KT 14
GTIN (EAN)	4032248945344
Qty.	1 pc(s).

KT 14

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	30 mm	Depth (inches)	1.181 inch
Height	63.5 mm	Height (inches)	2.5 inch
Width	225 mm	Width (inches)	8.858 inch
Net weight	324.78 g		

Technical data

Description of article	Cutting tool for up to 14 mm outside diameter	Version	One-hand mechanical
------------------------	---	---------	---------------------

Cutting tools

Copper cable - flexible, max.	70 mm ²	Copper cable - flexible, max. (AWG)	2/0 AWG
Copper cable - solid, max.	16 mm ²	Copper cable - solid, max. (AWG)	6 AWG
Copper cable - stranded, max.	35 mm ²	Copper cable - stranded, max. (AWG)	2 AWG
Copper cable, max. diameter	14 mm	Data / telephone / control cable, max. Ø	14 mm
Single-core aluminium cable, max.(mm ²)	35 mm ²	Stranded aluminium cable, max (mm ²)	70 mm ²
Stranded aluminium cable, max. (AWG)	2/0 AWG	Stranded aluminium cable, max. diameter	14 mm

Classifications

ETIM 6.0	EC000142	ETIM 7.0	EC000142
ETIM 8.0	EC000142	ETIM 9.0	EC000142
ECLASS 9.0	21-04-47-01	ECLASS 9.1	21-04-37-06
ECLASS 10.0	21-04-47-01	ECLASS 11.0	21-04-47-01
ECLASS 12.0	21-04-47-01	ECLASS 13.0	21-04-47-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Approvals

Approvals



Downloads

Approval/Certificate/Document of Conformity	Manufacturer's Declaration - Cable cutters
Catalogues	Catalogues in PDF-format
Brochures	

KT 14

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



max. 14 mm



max. 16 mm²



max. 35 mm²



max. 70 mm²

suggested cross-section range/
Empfohlener Querschnittsbereich