


SAI-M23-SE-9**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Pinning**

The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

General ordering data

Version	Sensor/Actuator plug-in connector, Insert
Order No.	1170050000
Type	SAI-M23-SE-9
GTIN (EAN)	4032248962167
Qty.	1 pc(s).

SAI-M23-SE-9

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	3 g
------------	-----

Technical data customisable plug-in connectors

Coding	none	Coding possibilities for M23 signal inserts	H-coded, N-coded, S-coded, X-coded, Y-coded
Housing main material	Thermoplastic polyamide PA 6, PBT	Number of poles	9
Plugging cycles	> 1000	Pollution severity	3
Rated current	2 mm contact= 20 A, 1 mm contact = 8 A	Rated voltage	200 V
Type of connection	Crimp connection		

Classifications

ETIM 6.0	EC000438	ETIM 7.0	EC003557
ETIM 8.0	EC003557	ETIM 9.0	EC003557
ECLASS 9.1	27-44-02-05	ECLASS 10.0	27-44-02-23
ECLASS 11.0	27-44-02-23	ECLASS 12.0	27-44-02-23
ECLASS 13.0	27-44-02-23		

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E344862

Downloads

Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

SAI-M23-SE-9

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany


www.weidmueller.com

Drawings

Pinning



Dimensioned drawing



Technical data

Technical data									
Number of positions	6	7	9		12	16	17	19	
Number of contacts	6	7	8	1	12	16	17	16	3
Contact ø	mm	2	2	1	2	1	1	1	1.5

