

ACT20M-RTI-AO-E-S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****ACT20M: The slim solution**

- Safe and space-saving (6 mm) isolation and conversion
- Quick installation of the power supply unit using the CH20M mounting rail bus
- Easy configuration via DIP switch or FDT/DTM software
- Extensive approvals such as ATEX, IECEx, GL, DNV
- High interference resistance

General ordering data

| | |
|------------|---|
| Version | Temperature converter, Without galvanic isolation, Input : Temperature, PT100, Output : I / U |
| Order No. | 1375520000 |
| Type | ACT20M-RTI-AO-E-S |
| GTIN (EAN) | 4050118259681 |
| Qty. | 1 pc(s). |

ACT20M-RTI-AO-E-S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|----------|-----------------|------------|
| Depth | 114.3 mm | Depth (inches) | 4.5 inch |
| Height | 112.5 mm | Height (inches) | 4.429 inch |
| Width | 6.1 mm | Width (inches) | 0.24 inch |
| Net weight | 86 g | | |

Temperatures

| | | | |
|---------------------|----------------|----------|--|
| Storage temperature | -40 °C...85 °C | Humidity | 40 °C / 93 % rel. humidity, no condensation |
|---------------------|----------------|----------|--|

Probability of failure

| | |
|------|-------|
| MTBF | 195 a |
|------|-------|

Input

| | | | |
|--|---|--------------------------------------|-----------------------|
| Influence of the sensor cable resistance | <0.002 Ω/Ω (@ 3/4-wire) | Line resistance in measuring circuit | ≤ 50 Ω |
| Number of inputs | 1 | Sensor | PT100 (2-/3-/4- wire) |
| Temperature input range | Configurable, PT100: -200...+850 °C, min. mea- surement range 10°C (RTD) | | |

Output

| | | | |
|------------------------|---|------------------------|---|
| Load impedance current | ≤ 600 Ω | Number of outputs | 1 |
| Output current | configurable, 0...20 mA, 4...20 mA | Output signal limit | <4 mA (average), <60 mA (pulse current), low duty cycle |
| Output voltage, note | configurable, 0(2)...10 V, 0(1)...5 V | Type | active, connected control must be passive |
| Wire break detection | Yes, Configurable, 3.5 mA / 23 mA / none | load impedance voltage | ≥ 10 kΩ |

General data

| | | |
|--------------------|---|------------------------|
| Accuracy | absolute accuracy: <±0.1 % of the measurement range | |
| Configuration | DIP switch | |
| Delivery state | Output: 4...20 mA // Sensor error detection: enabled // Output error level: downscale // Noise suppression: 50 Hz // Step response time: < 30 ms // Start temperature: -200 °C // End temperature: 0 °C | |
| Delivery state | Setting parameters | Output |
| | Configuration | 4...20 mA |
| | Setting parameters | Sensor error detection |
| | Configuration | enabled |
| | Setting parameters | Output error level |
| | Configuration | downscale |
| | Setting parameters | Noise suppression |
| | Configuration | 50 Hz |
| | Setting parameters | Step response time |
| | Configuration | < 30 ms |
| | Setting parameters | Start temperature |
| | Configuration | -200 °C |
| | Setting parameters | End temperature |
| | Configuration | 0 °C |
| Galvanic isolation | Without isolation | |

Creation date May 5, 2024 4:48:22 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

ACT20M-RTI-AO-E-S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

| | |
|-------------------------|---|
| Power consumption, max. | 0.5 W |
| Power consumption, typ. | 0.37 W |
| Rail | TS 35 |
| Step response time | Configurable, ≤ 30 ms, <300 ms |
| Temperature coefficient | ≤0.01 % of the measurement range/°C or 0.02 °C/°C |
| Voltage supply | 24 V DC ± 30 % |

Insulation coordination

| | | | |
|--------------------|--------------------|--------------------|-------------------|
| EMC standards | IEC 61326-1, NE 21 | Galvanic isolation | Without isolation |
| Pollution severity | 2 | | |

Data for Ex applications (ATEX)

| | | | |
|-----------------------|---------------------------------------|---------|------------------------|
| Installation location | Device installed in safe area, zone 2 | Marking | II 3 G Ex nA IIC T4 Gc |
|-----------------------|---------------------------------------|---------|------------------------|

Connection data

| | | | |
|---|---------------------|---|---------------------|
| Type of connection | Screw connection | Tightening torque, min. | 0.4 Nm |
| Tightening torque, max. | 0.6 Nm | Clamping range, rated connection | 2.5 mm ² |
| Clamping range, min. | 0.5 mm ² | Clamping range, max. | 2.5 mm ² |
| Wire connection cross section AWG, min. | AWG 30 | Wire connection cross section AWG, max. | AWG 14 |

EMC conformity and approvals

| | | | |
|---------------|--------------------|-----------|-------------|
| EMC standards | IEC 61326-1, NE 21 | Standards | IEC 61010-1 |
|---------------|--------------------|-----------|-------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002919 | ETIM 7.0 | EC002919 |
| ETIM 8.0 | EC002919 | ETIM 9.0 | EC002919 |
| ECLASS 9.0 | 27-21-01-29 | ECLASS 9.1 | 27-21-01-29 |
| ECLASS 10.0 | 27-21-01-29 | ECLASS 11.0 | 27-21-01-29 |
| ECLASS 12.0 | 27-21-01-29 | ECLASS 13.0 | 27-21-01-29 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 2f6dd957-421a-46db-a0c2-cf1609156924 |

Important note

| | |
|---------------------|---|
| Product information | <p>The ACT20M-RTI-AO-S configurable temperature transducer isolates and converts analogue signals. An analogue RTD input signal (Type Pt100) is linearly converted into an analogue output signal and galvanically isolated. The power supply is galvanically isolated from the input and output (3-way isolation) and this is done with direct wiring or over the Weidmüller rail bus.</p> <p>The ACT20M-RTI-AO-E-S configurable temperature transducer offers the same functionality but does not provide galvanic isolation.</p> |
|---------------------|---|

ACT20M-RTI-AO-E-S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E337701 |


Downloads

| | |
|---|---|
| Approval/Certificate/Document of Conformity | DNV-GL certificate FM certificate IECEXx certificate ATEX certificate Declaration of Conformity |
| Engineering Data | CAD data – STEP |
| Software | DIP switch configuration tool |
| User Documentation | instruction sheet |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

Dimensional drawing



example for DIP switch setting
(with ACT20M tool software)

ACT20M-RTI-AO-E-S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

ACT20 (incl. DIN rail bus & powersupplies)



Power supply adapter modules for separate supply and distribution of the supply voltage: for the ACT20 series/ MICROSERIES signal converters.

The 22.5/6.1 mm wide power-feed modules are mounted directly adjacent to the analogue signal converters. Then the 24 VDC supply voltage is optionally bridged via the CH20M (ACT20-series) rail bus or simply bridged over using the pluggable ZQV 4N (MICROSERIES) cross-connectors.

The ACT20-Feed-In-PRO-S can also detect faults coming from any of the devices mounted on the CH20 bus mounting profile.

In the event of an error or fault, the integrated status relay sends a common alarm to the external controller. In addition, two power supply units (as primary and backup supply) can be connected to the ACT20 Feed-In PRO-S.

Two feed-in modules mounted to the CH20 bus mounting profile guarantee a 100% redundant power supply.

Three LEDs are used to show the status of the power supply and error messages.

The ACT20M-Feed-In PRO can also be used in Ex zone2 / Division2 applications.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SET CH20M BUS 250MM TS ... | Version |
| Order No. | 1335150000 | OMNIMATE Housing - series CH20M, Length: 250 mm, Width: 25.1 |
| GTIN (EAN) | 4050118138382 | mm |
| Qty. | 1 pc(s). | |
| Type | SET CH20M BUS 250MM TS ... | Version |
| Order No. | 1335140000 | OMNIMATE Housing - series CH20M, Length: 250 mm, Width: 25.1 |
| GTIN (EAN) | 4050118138375 | mm |
| Qty. | 1 pc(s). | |
| Type | ACT20-FEED-IN-PRO-S | Version |
| Order No. | 8965500000 | Supply module, Distributes supply voltage to rail bus, Optional |
| GTIN (EAN) | 4032248785117 | connection of backup supply |
| Qty. | 1 pc(s). | |

ACT20M-RTI-AO-E-S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Blank**

MultiFit is the Weidmüller marker system used for other makes of terminals. Similar to the Weidmüller Dekafix, the markers of the MultiFit family are available ready-for-use with standard printing.

We recommend to carry out a test with sample markers on the terminals used when using MultiFit for the first time.

- One marker, suitable for different makes of terminals.
- Ready-to-use markers with standard printing
- Blank markers for printing with the PrintJet CONNECT or Plotter
- Delivery of individually printed markers according to customer CAE data or specifications
- One marking system for all applications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | MF 5/7.5 MC NE WS | Version |
| Order No. | 1877680000 | MultiFit, Terminal marker, 5 x 7.5 mm, Pitch in mm (P): 7.50 Adels |
| GTIN (EAN) | 4032248468270 | RKW, Phoenix, white |
| Qty. | 320 pc(s). | |