

**STRIPAX ULTIMATE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

**General ordering data**

Version	Tools, Stripping and cutting tool
Order No.	<a href="#">1468880000</a>
Type	STRIPAX ULTIMATE
GTIN (EAN)	4050118274158
Qty.	1 pc(s).

## STRIPAX ULTIMATE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	22 mm	Depth (inches)	0.866 inch
Height	99 mm	Height (inches)	3.898 inch
Width	190 mm	Width (inches)	7.48 inch
Net weight	174.63 g		

## Technical data

Description of article	Wire stripper unit
------------------------	--------------------

## Stripping tools

Cable type	Flexible and solid conductors with halogen-free insulation	Conductor cross-section (cutting capacity)	6 mm <sup>2</sup>
Conductor cross-section, max.	6 mm <sup>2</sup>	Conductor cross-section, min.	0.25 mm <sup>2</sup>
Stripping length, max.	25 mm	Stripping range AWG, max.	10 AWG
Stripping range AWG, min.	24 AWG		

## Classifications

ETIM 6.0	EC002109	ETIM 7.0	EC002109
ETIM 8.0	EC002109	ETIM 9.0	EC002109
ECLASS 9.0	21-04-37-06	ECLASS 9.1	21-04-37-06
ECLASS 10.0	21-04-37-06	ECLASS 11.0	21-04-37-06
ECLASS 12.0	21-04-37-06	ECLASS 13.0	21-04-37-06

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Product Change Notification	<a href="#">Technische Änderung für Abisolierwerkzeug Stripax</a> <a href="#">Technical change to stripping tool Stripax</a>
User Documentation	<a href="#">Manual</a> <a href="#">Library and function block – BDAL Stripax all version</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## STRIPAX ULTIMATE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



### Example of use



### Example of use



TYPE THHN

ALOGEN FREE 2,5MM<sup>2</sup> H07Z-K

**STRIPAX ULTIMATE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Accessories / replacement parts**

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

**General ordering data**

Type	ERME SPX UL	Version
Order No.	<a href="#">1471390000</a>	Accessories, Cutter holder
GTIN (EAN)	4050118278248	
Qty.	1 pc(s).	
Type	ERTE KLBC SPX UL	Version
Order No.	<a href="#">2571500000</a>	Accessories, Replacement clamping jaw
GTIN (EAN)	4050118582123	
Qty.	1 pc(s).	