

FAD S5115 HE20 16IO M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The front adapters for migration are connected to the old PLC and, by means of a new pre-assembled cable, to the new one. Some adapters have 2 connectors for redundancy.

General ordering data

Order No.	1986010000
Type	FAD S5115 HE20 16IO M
GTIN (EAN)	4050118371031
Qty.	1 pc(s).

FAD S5115 HE20 16IO M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	36 mm	Depth (inches)	1.417 inch
Height	280 mm	Height (inches)	11.024 inch
Width	46 mm	Width (inches)	1.811 inch
Net weight	195 g		

Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

Connection data

Connection (field side)	Plug-in connectors according to IEC 60603-13 / DIN 41651 20p
-------------------------	--

Ratings data

Operating voltage	30 V AC / 60 V DC	Max. current per channel	1 A
Max. current per byte	2 A	Total operating current	3 A

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	< 50 V AC
Surge voltage category	III	Pollution severity level	2
Insulation test voltage AC	0.35 kV		

Classifications

ETIM 6.0	EC002584	ETIM 7.0	EC002584
ETIM 8.0	EC002584	ETIM 9.0	EC002584
ECLASS 9.0	27-33-02-92	ECLASS 9.1	27-24-22-92
ECLASS 10.0	27-33-02-92	ECLASS 11.0	27-33-02-92
ECLASS 12.0	27-33-02-92	ECLASS 13.0	27-33-02-92

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	9d5ff7ee-74dc-449b-a1db-a29604b9b3e9

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity
Catalogues	Catalogues in PDF-format

FAD S5115 HE20 16IO M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

