

TRANSCLINIC 16I+**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**PV Solar String Monitoring System (PV Solar SMS)**

The PV Solar String Monitoring System is a new device developed to monitor currents and voltage at string level inside a combiner box.

This new device is able to monitor up to 32 strings and to measure up to 50A per string.

It can be directly powered by the solar array while providing reliable information and data.

In order to have a flexible design that can fit any customer requirements, the Solar String Monitoring System (Solar SMS) has been developed as a modular system.

It consists of:

- The Master Module, that includes the power supply and communication infrastructure (RS-485) to coordinate data gathering from sensors.
- The Slave Modules, that collect current data with the usage of hall effect sensors. These modules can mount 8 or 12 sensors each with 25A and 50A sensors respectively.

Solar SMS

General ordering data

Version	Photovoltaics
Order No.	2008130000
Type	TRANSCLINIC 16I+
GTIN (EAN)	4050118393903
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Alternative product	2433950000

TRANSCLINIC 16I+

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	92.2 mm	Height (inches)	3.63 inch
Width	109.5 mm	Width (inches)	4.311 inch
Length	368.9 mm	Length (inches)	14.524 inch
Net weight	939.34 g		

Temperatures

Continuous operating temp., min.	-25 °C	Continuous operating temp., max.	70 °C
Humidity at operating temperature	5 to 95 % (non-condensing)		

Technical data

Communication	MODBUS RS485 RTU	Height	≤ 3000 m
Maximum current per string	15 A DC (-25...+70 °C), 25 A DC (-25...+60 °C)	Maximum number of strings	16
Number of digital inputs	2	Pollution severity	2
Rated voltage	1000 V DC	Standards	IEC/ EN61010-1:2010, IEC/ EN61010-2-030:2010, EN61326-1:2013
String-current measurement error	± 300 mA from 3 A DC to 15 A DC	String-voltage measurement error	± 12 V from 100 V DC to 1000 V DC
Supply current	< 70 mA DC, 200 mA DC max.	Voltage supply	19.2 – 28.8 V DC
current measuring	Shunt resistance 1 mOhm		

Classifications

ETIM 6.0	EC002928	ETIM 7.0	EC002928
ETIM 8.0	EC002928	ETIM 9.0	EC002928
ECLASS 9.0	22-57-92-03	ECLASS 9.1	22-57-04-90
ECLASS 10.0	22-57-04-90	ECLASS 11.0	22-57-02-92
ECLASS 12.0	22-57-02-92	ECLASS 13.0	22-57-02-92

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	TRANSCLINIC 16I+
Engineering Data	CAD data – STEP
User Documentation	Manual Transclenic 16i+ family
Catalogues	Catalogues in PDF-format

TRANSCLINIC 16I+

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

