

ENERGY LOGGER D550**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Measuring instruments with a simple SO interface are widespread. However, they do not allow measured values to be passed directly into the internal network – so, until now, a gateway was required for each measuring instrument.

With the Energy Logger D550, pulse signals from up to 15 measuring instruments can be collected, saved and forwarded via a LAN interface.

The particularly compact Energy Logger D550 is the cost-effective solution to simplify and accelerate collection and forwarding of consumption and process data.

General ordering data

Order No.	2425520000
Type	ENERGY LOGGER D550
GTIN (EAN)	4050118433333
Qty.	1 pc(s).

ENERGY LOGGER D550

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	46 mm	Depth (inches)	1.811 inch
Height	90 mm	Height (inches)	3.543 inch
Width	107.5 mm	Width (inches)	4.232 inch
Net weight	200 g		

Temperatures

Storage temperature	-40 °C...70 °C	Operating temperature	-40 °C...55 °C
Humidity at operating temperature	5...95 % RH		

Communication

Interface	Protocol	Modbus RTU, Modbus-Gateway, Modbus TCP/IP, Modbus RTU over Ethernet, SNMP
	RS485: 9,6 – 115,2 kbps, Ethernet	

Inputs/outputs

Number of digital inputs	15	Number of digital outputs	3
Number of pulse outputs	3	Temperature input	Yes
Count rate	20 Hz		

Measurement data recording

Memory; minimum and maximum values	Yes	Memory size	32 MB
Software	ecoExplorer go®		

Technical data

Protection degree	IP20	Version	Power measurement/display for 1-, 3-phase mains
Standards	DIN EN 61326-1, DIN EN 61000-4-2, DIN EN 61000-4-3, DIN EN 61000-4-4, DIN EN 61000-4-5, DIN EN 61000-4-6, EN 61000-4-11, IEC 61010-1, IEC 61010-2-030, EN 55011	Surge voltage category	300 V CAT III
Voltage supply	20 - 250 V AC, 20 - 300 V DC20 - 300 V DC	Operating-hours counter	Yes

Insulation coordination

Surge voltage category	300 V CAT III
------------------------	---------------

Classifications

ETIM 6.0	EC002301	ETIM 7.0	EC002301
ETIM 8.0	EC002301	ETIM 9.0	EC002301
ECLASS 9.0	27-14-23-30	ECLASS 9.1	27-21-03-01
ECLASS 10.0	27-14-23-30	ECLASS 11.0	27-14-23-30
ECLASS 12.0	27-14-23-30	ECLASS 13.0	27-14-23-30

ENERGY LOGGER D550**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E469563

Downloads

Approval/Certificate/Document of Conformity	Application notes – Declaration of Conformity
Engineering Data	CAD data – STEP
Software	Win64 - ecoExplorer go Device description – MODBUS address list
User Documentation	Quick Guide German/English Manual Energy Logger D550 German/English Application notes – Manual ECOEXPLORER GO English
Catalogues	Catalogues in PDF-format

ENERGY LOGGER D550

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

