

IE-SR-2GT-LTE/4G-EU-M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Weidmüller Industrial Security Routers**

- Secure networks
 - Stateful packet inspection Firewall
 - IP/Port- forwarding
 - Network segmentation
- Easy integration of machine networks into manufacturing networks through 1: 1 NAT
- Secure and easy remote maintenance with Weidmüller u-link remote access service
- Enable modular and future proof network architectures with static and dynamic routing
- Secure communication over the Internet by using IPsec and OpenVPN
- Reliable internet connection, even without on-site internet access, thanks to integrated 4G/LTE cellular modem
- Full flexibility thanks to Fast Ethernet and Gigabit Ethernet interfaces ranging from 2 up to 4 ports.

General ordering data

Version	Security/NAT/VPN/U-link Router, with integrated multi-band modem (4G/3G/2G), EU-model, Gigabit Ethernet, 2 * RJ45 10/100/1000BaseT(X), DNV, IP20, -20 °C...70 °C
Order No.	2535970000
Type	IE-SR-2GT-LTE/4G-EU-M
GTIN (EAN)	4050118547641
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2022-10-31

IE-SR-2GT-LTE/4G-EU-M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	136 mm	Depth (inches)	5.354 inch
Height	170 mm	Height (inches)	6.693 inch
Width	57 mm	Width (inches)	2.244 inch
Net weight	700 g		

Temperatures

Storage temperature	-20 °C...85 °C	Operating temperature	-20 °C...70 °C
Humidity	5 - 90 %, no condensation		

Mobile radio interface

Frequency band	EMEA/Australia: LTE: 2 100 MHz (B1), 1800 MHz (B3), 2600 MHz (B7), 900 MHz (B8), 800 MHz (B20); UMTS/WCDMA: 2 100 MHz (B1), 1900 MHz (B2), 850 MHz (B5), 900 MHz (B8); GSM/GPRS/EDGE: Quad-Band (850/900/1800/1900 MHz)		
Mode of operation	Permanent connection, Manual connection control via web interface, Fallback connection with active ICMP monitoring of the target IP via Ethernet		
Transmission rate mobile radio	LTE category	CAT 4	
	Download rate, max.	150 Mbit/s	
	Upload rate, max.	50 Mbit/s	
Wireless module	LTE / HSPA+ multiband wireless module (4G / 3G / 2G) for fast wireless Internet access		

Network Services/Firewall/Management

Firewall	IPv4 Stateful Packet Inspection Firewall (incoming/outgoing), NAT masquerading, 1:1 NAT, Port forwarding, layer 2/3 filter (VLAN ID, VLAN QoS Tag, MAC address, EtherType frame), Auto-learning function to create packet filter rules (analysis of network traffic), Layer 2/3-based packet prioritisation (Ethernet Frame, IP Header, VLAN Tag)	Management	Configuration via WEB interface (HTTP/HTTPS), Language interface can be switched to German or English, Configuration support through detailed help information (tool tip), Configurable multi-user access with freely definable rights, Support for SNMP v1/v2/v3, event log/syslog
Network services	DHCP Server / DHCP Relay, DNS relay, NTP client, DynDNS (DHCP client acc. to RFC 2136)		

IE-SR-2GT-LTE/4G-EU-M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

VPN

IPsec	Configurable as IPsec server or client, Authentication via PSK (userid, password) or X.509 certificates, Hardware-based encryption for faster data throughput, Maximum 64 simultaneous connections (sub-network to sub-network or as IPsec server), Encryption algorithms DES-56, 3DES-168, AES-128, AES-192, AES-256	OpenVPN	Configurable as OpenVPN server or client (Layer 2 and Layer 3), Authentication via X.509 certificate, Tunnel support via HTTP proxy, Maximum 10 different client or server configurations, Unlimited number of client connections in server mode
u-link	OpenVPN-based remote access service via the Weidmüller u-link cloud		

Miscellaneous

Diagnostics	Remote capture function for network diagnostics via a connected PC (Wireshark)	Modbus/TCP	Integrated Modbus-TCP server for status queries and software-based enabling/disabling of VPN connections
Monitoring	Client monitoring (per ICMP) with alarm function in the event of a fault		

Modes of operation

IP router	IP routing (IPv4, Layer-3) with SPI firewall (Stateful Packet Inspection)	Transparent bridge	2-port switch with additional layer-2 filter
-----------	---------------------------------------------------------------------------	--------------------	----------------------------------------------

EMC conformity and approvals

EMC standards	FCC Part 15, Class A, EN 55032, EN 61000-4-2, -3, -4, -5, -6	Ship use	DNV
Shock	according to IEC 60068-2-27	Vibration	according to IEC 60068-2-6

Environmental conditions

Humidity	5 - 90 %, no condensation	
Operating altitude	Altitude, max.	2,000 m
	Note	in acc. with UL
	Altitude, max.	6,000 m
	Note	for restrictions, see the manufacturer's declaration for operating altitude in section downloads
Operating temperature, max.	70 °C	
Operating temperature, min.	-20 °C	
Safety distance to the compass	17 cm	
Storage temperature, max.	85 °C	
Storage temperature, min.	-20 °C	

IE-SR-2GT-LTE/4G-EU-M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Guarantee

Time interval	3 years
---------------	---------

Interfaces

Connector for external antennas		Digital inputs	Cut: physically disconnects (Link Down) the WAN port (24 V in), VPN-initiate: establishes a pre-configured VPN connection (24 V in)
	2x SMA female		
Digital outputs	Alarm: indicates a configurable network state or fault (24 V out), VPN-active: indicates an active VPN connection (24 V out)	Function reset button	Restoration of factory settings
LED indicator	Indication of voltage status, Status, CUT, Alarm, Active VPN connection, Mobile radio connection, Port LED: Link/ACT, Speed (RJ45 port)	Number of SCM-Card slots	1
Number of SIM-Card slots	1	Number of ports	2 * RJ45 10/100/1000BaseT(X)
RJ45 ports	10/100/1000BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port	SCM-Card slot type	Smart Card (ID-000 format), Save and restore the configuration using smart card (memory chip)
SIM-Card slot type	Mini-SIM (ID-000 format)	USB port	USB 2.0 interface for firmware update or restoration of the device configuration via USB flash drive

Power supply

Connection type	1 removable 3-pin terminal block	
Current consumption	Voltage	24 V
	Current	0.6 A
Galvanic isolation	24: 24 V electrically isolated DC/DC converter	
Voltage supply	24 V DC, 1 single input	
Voltage supply range	Voltage type	DC
	Voltage, min.	7 V
	Voltage, max.	36 V

Technical data

Housing main material	diecast aluminium	Protection degree	IP20
Speed	Gigabit Ethernet	Type of mounting	DIN rail, VESA 75

IE-SR-2GT-LTE/4G-EU-M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Technology

Standard	<p>LTE: 3GPP Release 9, UMTS: 3GPP Releases 5, 6, 7, 8, GSM/GPRS/EDGE: 3GPP Release 99, GERAN Feature Package #1, CD- MA (Americas): TIA/EIA/ IS-2000.1 through .6. cd- ma2000® Standards for Spread Spectrum Systems. Release 0. April 2000; TIA/EIA/IS-2000.1-1 through .6-1. cdma2000® Addendum 1 April 2000; TIA/EIA/IS-2000.1-2 through .6-2. cdma2000® Addendum 2 June 2001; TIA/EIA/IS-95-B. Mobile Station-Base Station Com- patibility Standard for Dual- Mode Spread Spectrum Systems. December 4, 1998; TIA/EIA/IS-. cd- ma2000® High Rate Pack- et Data Air Interface Speci- fication. Nov. 2000</p>
----------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

WLAN interface

Transmission rate	<p>Max. download rate: 100 Mbps, Max. upload rate: 50 Mbps</p>
-------------------	------------------------------------------------------------------------

Classifications

ETIM 6.0	EC001478	ETIM 7.0	EC001478
ETIM 8.0	EC001478	ETIM 9.0	EC001478
ECLASS 9.0	19-17-01-03	ECLASS 9.1	19-17-01-03
ECLASS 10.0	19-17-04-05	ECLASS 11.0	19-17-04-05
ECLASS 12.0	19-17-04-05	ECLASS 13.0	19-17-04-05

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	9229992a-00b9-4096-8962-200a7f33e289

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

Creation date April 26, 2024 1:07:54 PM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

IE-SR-2GT-LTE/4G-EU-M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Con- formity	DNV-GL certificate Manufacturer's declaration for operating altitude
Engineering Data	CAD data – STEP
Product Change Notification	Firmware Release Notes
Software	Software – Router Search Utility Device description – SNMP MIB file Firmware – Current Firmware
User Documentation	Hardware Installation Guide Manual u-link Technical User Guide User Note - Secure Router Configuration
Catalogues	Catalogues in PDF-format

IE-SR-2GT-LTE/4G-EU-M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

u-link Remote Access Service



The Weidmüller u-link remote access service offers an easy possibility to securely access ethernet devices in a remote network.

With the u-link VPN Server as the central meeting point server, the VPN clients (service PC and Weidmüller u-link client devices) always connect outbound and thus conform to the typical IT security requirements. Separate database and server instances are used for each u-link customer account (secure client isolation) to ensure data integrity.

Communication between the u-link VPN server and remote clients (service PCs and u-link client devices) takes place via a certificate-protected openVPN connection. The u-link creed is "configuration instead of programming" the use is intuitive and does not require expert knowledge.

Featureset:

- 1-click VPN remote access for service PC's
- easyAccess: web, rdp or vnc connections to remote hosts fully browser based for use with tablet or smartphone
- Organization and Group Management
- Topologies including 3rd party end-devices
- Firmware management: Display of firmware status of all routers and the option of a time-controlled, automated firmware update
- Individual access rights: granular configuration of access rights to devices in the target network
- Extensive event log: Presentation of all activities in the u-link portal with extensive filter and export functions
- Password policy: Increased security through configurable specification of minimum requirements for password quality and validity period

Weidmüller offers the following usage variations and additional options for the u-link Remote Access Service:

Basic version:

- Automatically assigned by registering at u-link.weidmueller.com
- Free use for 6 months, extended to 365 days when registering a new u-link client device
- Full featureset
- Unlimited users
- Max. 50 u-link capable devices (access points to a remote network)
- 1 simultaneous VPN connection
- No data or speed limitations (subject to normal market usage)

Extensions

- Additional 50/100/250/500/1000 or more u-link capable devices
- Additional simultaneous VPN connections
- China-VPN: secure and reliable VPN connection to and from China

General data April 26, 2024 1:07:54 PM CEST

Type	U-LINK-LIC-STD-50-1Y	Version
Order No.	2status 20.04.2024 / We reserve the right to make technical changes.	
GTIN (EAN)	4050118682298	Service. Can be used to upgrade an entry version or to extend period

IE-SR-2GT-LTE/4G-EU-M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	U-LINK-LIC-STD-150-1Y	Version
Order No.	2447050000	"Standard 150" version software licence for u-link Remote Access
GTIN (EAN)	4050118461602	Service. Can be used to upgrade an entry version or "Standard 50"
Qty.	1 pc(s).	version or to extend the period of a "Standard 150" version"
Type	U-LINK-LIC-STD-500-1Y	Version
Order No.	2457850000	"Standard 500" version software licence for u-link Remote Access
GTIN (EAN)	4050118472851	Service. Can be used to upgrade an entry version or "Standard
Qty.	1 pc(s).	150/300" versions or to extend period of a "Standard 300" version
Type	U-LINK-LIC-VPN-1Y	Version
Order No.	2447060000	"VPN connection" licence code for u-link Remote Access Service. Can
GTIN (EAN)	4050118461497	be used as an additional VPN connection or to extend the period of a
Qty.	1 pc(s).	VPN connection that has already been activated
Type	U-LINK-LIC-STD-300-1Y	Version
Order No.	2457840000	"Standard 300" version software licence for u-link Remote Access
GTIN (EAN)	4050118472844	Service. Can be used to upgrade an entry version or "Standard 150"
Qty.	1 pc(s).	version or to extend the period of a "Standard 300" version"

Ethernet



- Suitable for Cat. 5 (up to 100 MHz) and Cat. 6 (up to 250 MHz Class E)
- Suitable for PoE+ (according to IEEE 802.3at, IEEE 802.3bt Type 3 and 4)
- Protection of all wire pairs
- Connection via RJ45 sockets
- Metal housing

General ordering data

Type	VDATA CAT6	Version
Order No.	1348590000	Terminal rail fixing, Surge protection, Cat.6, PoE, 802.3 bt at Type 1,
GTIN (EAN)	4050118153002	802.3 bt at Type 2, 802.3 bt at Type 3, 802.3 bt at Type 4
Qty.	1 pc(s).	

IE-SR-2GT-LTE/4G-EU-M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Mounting kit for 19" rack assembly

- For assembling DIN rail-based devices on 19" racks



General ordering data

Type	RM-KIT	Version
Order No.	1241440000	Kit for 19"-rack mounting
GTIN (EAN)	4050118029154	
Qty.	1 pc(s).	

Antennas and antenna accessories (coax cables and mounts)



Antennas and antenna accessories (coax cables and mounts)

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

General ordering data

Type	IE-ANT-CELL/WL-MB-MIMO- ...	Version
Order No.	2788090000	Omni-directional antenna, Cellular antenna, Wi-Fi antenna, Up to 5G
GTIN (EAN)	4064675066354	(NR), Up to Wi-Fi 6 & 6E (IEEE802.11ax), Linear, Vertical, 2x SMA
Qty.	1 pc(s).	male, 2x RP-SMA male, IP67, Impedance: 50 Ω
Type	IE-ANT-3G-806-2170-2-NF	Version
Order No.	1491160000	Mobile radio antenna, Omni-directional antenna, Gain of up to 2 dBi,
GTIN (EAN)	4050118300710	Vertical, Linear, 1x N-type female, bottom, IP54, , Impedance: 50 Ω
Qty.	1 pc(s).	
Type	IE-ANT-CELL-MIMO-DO-SMAM	Version
Order No.	2788120000	Omni-directional antenna, Cellular antenna, Up to 5G (NR), Linear,
GTIN (EAN)	4064675066385	Vertical, 2x SMA male, IP67, Impedance: 50 Ω
Qty.	1 pc(s).	
Type	IE-ANT-CELL-SISO-EO-SMAM	Version
Order No.	2788130000	Omni-directional antenna, Cellular antenna, Up to 5G (support for
GTIN (EAN)	4064675066392	frequencies below 2.7 GHz, e.g., bands n1, n2, n28), Vertical, SMA
Qty.	1 pc(s).	male, IP66, Impedance: 50 Ω

IE-SR-2GT-LTE/4G-EU-M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

Type	IE-ANT-CELL-SISO-LO-NF	Version
Order No.	2788150000	Omni-directional antenna, Cellular antenna, Up to 5G (NR), Vertical, N
GTIN (EAN)	4064675066415	female, IP66, Impedance: 50 Ω
Qty.	1 pc(s).	

Type	IE-ANT-3G-806-2500-4-NF	Version
Order No.	1491170000	Mobile radio antenna, Omni-directional antenna, Gain of up to 4 dBi,
GTIN (EAN)	4050118300727	Vertical, Linear, 1x N-type female, bottom, IP66, , Impedance: 50 Ω
Qty.	1 pc(s).	