

IE-SW-EL18-16TX-2GC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Features of EcoLine unmanaged Switch series**

- Huge variety of port count and media type enable a wide range of applications (5 to 24 ports)
- Models supporting Gigabit Ethernet including Jumbo Frame support for applications with high demand on bandwidth and latency
- Suitable for use in harsh industrial environment thanks to rugged design and wide operating temperature range of -40°C up to 75°C
- Reliable operation due to redundant voltage inputs, fault relay and LED diagnostics

General ordering data

Version	Network switch, unmanaged, Fast/Gigabit Ethernet, Number of ports: 16x RJ45 10/100BaseT(X), 2x combo-ports (10/100/1000BaseT(X) or 1000BaseSFP), IP30, -40 °C...75 °C
Order No.	2682200000
Type	IE-SW-EL18-16TX-2GC
GTIN (EAN)	4050118692518
Qty.	1 pc(s).

IE-SW-EL18-16TX-2GC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	108.5 mm	Depth (inches)	4.272 inch
Height	154 mm	Height (inches)	6.063 inch
Width	96.4 mm	Width (inches)	3.795 inch
Net weight	1,363 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...75 °C
Humidity	5 to 95 % (non-condensing)		

EMC conformity and approvals

EMC standards	EN 55032, EN 55024, CISPR 32, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 4 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz bis 1 GHz: 3 V/m, IEC 61000-4-4 EFT: Power: 0.5 kV; Signal: 0.5 kV, IEC 61000-4-5 Surge: Power: 0.5 kV; Signal: 1 kV, IEC 61000-4-6 CS: 3 Vrms	Free fall	
Safety standard	UL 61010-1, UL 61010-2-201	Shock	According to IEC 60068-2-31 according to IEC 60068-2-27
Vibration	according to IEC 60068-2-6		

Environmental conditions

Humidity	5 to 95 % (non-condensing)		
Operating altitude	Altitude, max.	2,000 m	
	Note	in acc. with UL	
	Altitude, max.	6,000 m	
	Note	for restrictions, see the manufacturer's declaration for operating altitude in section downloads	
Operating temperature, max.	75 °C		
Operating temperature, min.	-40 °C		
Storage temperature, max.	85 °C		
Storage temperature, min.	-40 °C		

Guarantee

Time interval	5 years
---------------	---------

IE-SW-EL18-16TX-2GC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Interfaces

Fibre-optic ports	1000BaseSFP-Slot	LED indicator	Port LED: Link/ACT, FDX (RJ45 port)
Number of ports	16x RJ45 10/100BaseT(X), 2x combo-ports (10/100/1000BaseT(X) or 1000BaseSFP)	RJ45 ports	10/100BaseT(X) or 10/100/1000BaseT(X), auto negotiation, Full-/half- duplex mode, Auto MDI/ MDI-X port
Signalling contact	1 relay output with a cur- rent capacity of 1 A at 24 V DC		

MTBF

MTBF	According to Standard	Telcordia SR-332
	Operating time (hours), min.	748,087 h

Power supply

Connection type	1 removable 6-pin terminal block	
Current consumption	Voltage	24 V
	Current	0.35 A
Overload current protection	Yes	
Reverse polarity protection	Yes	
Voltage supply	12/24/48 V DC, 2 redundant inputs	
Voltage supply range	Voltage type	DC
	Voltage, min.	10.8 V
	Voltage, max.	52.8 V

Switch characteristics

Bandwidth backplane	7.2 Gbit/s	MAC table size	8 K
Packet buffer size	1 Mbit		

Technical data

Housing main material	Metal	Protection degree	IP30
Speed	Fast/Gigabit Ethernet	Switch	unmanaged
Type of mounting	DIN rail		

Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control
Standard	IEEE 802.3 for 10BASE-T, IEEE 802.3u for 100BASE- TX, IEEE 802.3ab for 1000BASE-T, IEEE 802.3z for 1000BASE-X, IEEE 802.3x for flow control		

Classifications

ETIM 6.0	EC000734	ETIM 7.0	EC000734
ETIM 8.0	EC000734	ETIM 9.0	EC000734
ECLASS 9.0	19-17-01-06	ECLASS 9.1	19-17-01-06
ECLASS 10.0	19-17-04-02	ECLASS 11.0	19-17-04-02
ECLASS 12.0	19-17-04-02	ECLASS 13.0	19-17-04-02

Creation date May 10, 2024 5:11:07 PM CEST

IE-SW-EL18-16TX-2GC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	9229992a-00b9-4096-8962-200a7f33e289

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

Downloads

Approval/Certificate/Document of Conformity	KC certificate EU Declaration of Conformity RCM Declaration of Conformity UK Declaration of Conformity Manufacturer's declaration for operating altitude
Engineering Data	CAD data – STEP
User Documentation	Hardware Installation Guide
Catalogues	Catalogues in PDF-format

IE-SW-EL18-16TX-2GC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

SFP transceiver (for use with switches of Eco- Advanced- and SubstationLine)



Features of SFP-Transceiver series

- Huge variety of transceiver types for several transmission speeds (up to 10 Gigabit Ethernet) and distances (up to 60 km)
- BiDi SFP models for communication via single fiber
- Easy control of transceiver status due to support of Digital Diagnostic Monitoring (DDM)
- Hot pluggable (during operation)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Eco-, Advanced- and SubstationLine

General ordering data

Type	IE-SFP-1GE-SM-10-BIDI-T ...	Version
Order No.	2682520000	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 10 km,
GTIN (EAN)	4050118692198	-40 °C...85 °C
Qty.	1 pc(s).	
Type	IE-SFP-1GE-SM-20-BIDI-T ...	Version
Order No.	2682540000	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 20 km,
GTIN (EAN)	4050118692174	-40 °C...85 °C
Qty.	1 pc(s).	
Type	IE-SFP-1GE-SM-10	Version
Order No.	2682500000	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 10 km, -40
GTIN (EAN)	4050118692211	°C...85 °C
Qty.	1 pc(s).	
Type	IE-SFP-1GE-SM-40	Version
Order No.	2682510000	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 40 km, -40
GTIN (EAN)	4050118692204	°C...85 °C
Qty.	1 pc(s).	
Type	IE-SFP-1GE-MM-2	Version
Order No.	2682490000	SFP Transceiver, 1000 Mbps, Multimode, LC-Duplex, 2 km, -40 °C...85
GTIN (EAN)	4050118692228	°C
Qty.	1 pc(s).	
Type	IE-SFP-1GE-SM-10-BIDI-T ...	Version
Order No.	2682530000	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 10 km,
GTIN (EAN)	4050118692181	-40 °C...85 °C
Qty.	1 pc(s).	
Type	IE-SFP-1GE-SM-20-BIDI-T ...	Version
Order No.	2682550000	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 20 km,
GTIN (EAN)	4050118692167	-40 °C...85 °C
Qty.	1 pc(s).	
Type	IE-SFP-1GE-MM-05	Version
Order No.	2682480000	SFP Transceiver, 1000 Mbps, Multimode, LC-Duplex, 0.5 km, -40
GTIN (EAN)	4050118692235	°C...85 °C
Qty.	1 pc(s).	

IE-SW-EL18-16TX-2GC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Mounting kit for 19" rack assembly**

- For assembling DIN rail-based devices on 19" racks

**General ordering data**

Type	RM-KIT	Version
Order No.	1241440000	Kit for 19"-rack mounting
GTIN (EAN)	4050118029154	
Qty.	1 pc(s).	