

ACT20P-VMR-3PH-ILP-H-S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****ACT20P: The flexible solution**

- Precise and highly functional signal converters
- Release levers simplify handling

General ordering data

Version	Limit value monitoring, Input : 180...500 V AC, Output : 2 x relays, Input: 3-phase voltage, Relay output
Order No.	7760054165
Type	ACT20P-VMR-3PH-ILP-H-S
GTIN (EAN)	6944169689086
Qty.	1 pc(s).

ACT20P-VMR-3PH-ILP-H-S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	114.3 mm	Depth (inches)	4.5 inch
Height	117 mm	Height (inches)	4.606 inch
Width	22.5 mm	Width (inches)	0.886 inch
Net weight	233 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-20 °C...65 °C
Humidity at operating temperature	0...95 % (no condensation)	Humidity	5...85 % rel. humidity, no condensation

Probability of failure

SIL in compliance with IEC 61508	None
----------------------------------	------

Input

Input frequency	40...60 Hz	Input measurement range	200...480 VAC
Input resistance, voltage	$\geq 1,8 M\Omega$	Input voltage	180...500 VAC
Number of inputs	1	Type	3-phase or 3-phase plus zero conductor, AC voltage

Output

Number of outputs	2
-------------------	---

Output (digital)

Alarm function	Top and bottom limit values, window range, Holding function can be activated, Phase error, Phase sequence, Asymmetry, Alarm delay: 0...10 s	Hysteresis	5 % @ Phase asymmetry
Max. switching frequency	20 Hz	Max. switching voltage, AC	250 V
Max. switching voltage, DC	30 V	Number of digital outputs	2
Rated switching current	5 A	Switch-on delay	0...10 s, configurable
Switching thresholds	Adjustable, MIN = 50... 100 % x U_{Rated} input voltage (undervoltage alarm), MAX = 70...120 % x U_{Rated} input voltage (overvoltage alarm)	Type	2 x 1 - or 1 x 2 changeover contact relay, Relay polarity can be inverted

General data

Accuracy	3 % * U_{rated} voltage	Configuration	DIP switch and potentiometer
Galvanic isolation	2-way isolator, between input/output, yes, between input / output / supply	Long-term drift	0.1 % / 10.000 h
Power consumption	$\leq 3VA$, $<2 W$	Rail	TS 35
Repeat accuracy	2 % * U_{rated} voltage	Step response time	$\leq 100 ms$
Temperature coefficient	350 ppm/K	Voltage supply	supplied from voltage measurement inputs

ACT20P-VMR-3PH-ILP-H-S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Insulation coordination

EMC standards	EN 61326-1	Galvanic isolation	2-way isolator, between input/output, yes, between input/output/supply
Impulse withstand voltage	6 kV (input - output), 4 kV (output 1 - output 2), 1.2/50 µs	Insulation voltage	2.5 kV (input / output)
Pollution severity	2	Rated voltage	600 VAC (input - output), 300 VAC (output 1 - output 2)
Surge voltage category	III	Test voltage	0.5 kV

Connection data

Type of connection	Screw connection	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.6 Nm	Clamping range, rated connection	1.5 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	2.5 mm ²
Wire connection cross section AWG, min.	AWG 26	Wire connection cross section AWG, max.	AWG 12

Classifications

ETIM 6.0	EC002654	ETIM 7.0	EC002654
ETIM 8.0	EC002654	ETIM 9.0	EC002654
ECLASS 9.0	27-21-01-22	ECLASS 9.1	27-21-01-22
ECLASS 10.0	27-21-01-22	ECLASS 11.0	27-21-01-22
ECLASS 12.0	27-21-01-22	ECLASS 13.0	27-21-01-22

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2f6dd957-421a-46db-a0c2-cf1609156924

Important note

Product information	<p>ACT20P-VMR-3PH-ILP-H is a three-phase voltage setpoint limit monitor relay (3-phase or 3-phase plus zero conductor). The device is powered by the input measuring circuit. The device incorporates two separate relay outputs which trigger an alarm upon phase asymmetry, phase loss, phase sequence errors and phase angle errors and when exceeding or falling below preset voltage limit values. The alarm can also be set to trigger after an adjustable time delay.</p> <p>Features</p> <ul style="list-style-type: none"> • Supply from the input measuring circuit • Manual front-sided configuration via DIP switch, potentiometer and rotary switch • Various alarm functions: phase asymmetry, phase loss, phase sequence errors, phase angle errors, alarm delay, upper/lower limit value alarm, window alarm • Front LEDs indicates operation status and malfunction. • 3-way galvanic isolation between input, output 1 and output 2.
---------------------	---

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E469563

ACT20P-VMR-3PH-ILP-H-S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity

[Application notes – Declaration of Conformity](#)

Engineering Data

[CAD data – STEP](#)

Software

[DIP switch configuration tool](#)

User Documentation

[Instruction sheet](#)

Catalogues

[Catalogues in PDF-format](#)


ACT20P-VMR-3PH-ILP-H-S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings


Connection diagram




Dimensioned drawing





Overvoltage alarm (O)



Undervoltage alarm (U)



Window alarm (W)



example for DIP switch setting (with ACT20 tool)

ACT20P-VMR-3PH-ILP-H-S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Blank**

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	ESG 6.6/20 BHZ 5.00/04	Version
Order No.	1082540000	ESG, Device markers x 20 mm, PA 66, Colour: white
GTIN (EAN)	4032248845439	
Qty.	200 pc(s).	

ACT20P-VMR-3PH-ILP-H-S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Blank**

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	ESG 8/13.5/43.3 SAI AU	Version
Order No.	1912130000	ESG, Device markers x 13.5 mm, PA 66, Colour: Transparent
GTIN (EAN)	4032248541164	
Qty.	5 pc(s).	