

SKH2 F32 (Z+B) LPP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



Plug-in card holders are used to adapt cards from the Euro format (19") to connectors in compliance with IEC 603/ DIN 41612 and DIN 41617.

Plug-in card holders consist of the following components:

- Circuit board with standard connectors and inserts with clamping-yoke connection.
- Flange housing and holder/pull-out mechanism for the circuit card.
- Plug-in card and mounting foot for attaching to mounting rail or directly to panel.

The plug-in card holders are normally used in the following cases:

- For quick adaptation in industrial applications of different 19" modules, and for avoiding the expense of a 19" rack.
- When there are only a few cards to install and connect.
- The circuit board is located in a remote position where the cabling cannot be easily handled.
- An older system needs to be updated with additional electronics modules.
- For test devices, production processes and laboratories: where circuit boards need to be swapped out quickly and connections must be easy to handle.

General ordering data

| | |
|------------|---|
| Version | Interface, Plug-in connector, acc. to DIN 41612 female, 32F |
| Order No. | 8174850000 |
| Type | SKH2 F32 (Z+B) LPP |
| GTIN (EAN) | 4008190169343 |
| Qty. | 1 pc(s). |

SKH2 F32 (Z+B) LPP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 193 mm | Depth (inches) | 7.598 inch |
| Height | 81 mm | Height (inches) | 3.189 inch |
| Width | 160 mm | Width (inches) | 6.299 inch |
| Net weight | 381 g | | |

Temperatures

| | | | |
|---------------------|-------------|-----------------------|-----------|
| Storage temperature | -40...60 °C | Operating temperature | 0...55 °C |
|---------------------|-------------|-----------------------|-----------|

Connection data

| | | | |
|--------------------------------|----------------|-------------------------------|---|
| Connection (field side) | LP 5.08mm | Connection on control side | Plug-in connector, acc. to DIN 41612 female |
| Contact assembly | z and b | Design of the pluggable board | 100x160 mm euro format for 19" racks |
| Number of poles (control side) | 32-pole female | Type (control side) | 32F |

Rating data

| | | | |
|---------------|----------|------------------------------|-----|
| Rated voltage | 250 V UC | Rated current per connection | 4 A |
|---------------|----------|------------------------------|-----|

Insulation coordination (EN50178)

| | | | |
|-------------------------------|--------------|----------------------------|--------|
| According to | DIN EN 50178 | Rated insulation voltage | 250 V |
| Surge voltage category | II | Pollution severity level | 2 |
| Pulse voltage test (1,2/50µs) | 2.1 kV | Insulation test voltage AC | 1.2 kV |

Connection field

| | | | |
|----------------------------------|---------------------|------------------------------|---------------------|
| Clamping range, max. | 6 mm ² | Clamping range, min. | 0.5 mm ² |
| Flexible with sleeve, max. | 2.5 mm ² | Flexible with sleeve, min. | 0.5 mm ² |
| Flexible, max. H05(07) V-K | 4 mm ² | Flexible, min. H05(07) V-K | 0.5 mm ² |
| Max. wire cross-section, AWG | AWG 12 | Min. wire cross-section, AWG | AWG 26 |
| Sleeve with plastic collar, max. | 2.5 mm ² | Solid, max. H05(07) V-U | 6 mm ² |
| Solid, min. H05(07) V-U | 0.5 mm ² | Stripping length | 6 mm |
| Tightening torque, max. | 0.6 Nm | Tightening torque, min. | 0.5 Nm |
| Type of connection | Screw connection | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002780 | ETIM 7.0 | EC002780 |
| ETIM 8.0 | EC002780 | ETIM 9.0 | EC002780 |
| ECLASS 9.0 | 27-14-11-52 | ECLASS 9.1 | 27-24-22-92 |
| ECLASS 10.0 | 27-14-11-52 | ECLASS 11.0 | 27-14-11-52 |
| ECLASS 12.0 | 27-14-11-52 | ECLASS 13.0 | 27-14-11-52 |

Environmental Product Compliance

| | |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

SKH2 F32 (Z+B) LPP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity

[Declaration of Conformity](#)

Product Change Notification

[20211110 Technical change to SKH interfaces!](#)

Catalogues


[Catalogues in PDF-format](#)

SKH2 F32 (Z+B) LPP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



SKH2 F32 (Z+B) LPP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Steel



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | TS 35X7.5 2M/ST/ZN | Version |
| Order No. | 0383400000 | Terminal rail, without slot, Accessories, 35 x 7.5 x 2000 mm, Steel, |
| GTIN (EAN) | 4008190088026 | galvanic zinc plated and passivated |
| Qty. | 2 m | |
| Type | TS 35X15/2.3 2M/ST/ZN | Version |
| Order No. | 0498000000 | Terminal rail, without slot, Accessories, 35 x 15 x 2000 mm, Steel, |
| GTIN (EAN) | 4008190042493 | galvanic zinc plated and passivated |
| Qty. | 2 m | |