

MULTIMETER 1037**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Multimeters are capable of measuring a number of variables. Each instrument can measure voltage and resistance, as well as performing continuity and diode testing as standard.

In addition, the individual multimeters also feature extra measuring options such as current, frequency, capacitance and temperature. Digital multimeters have the advantage of a clear display which can be read easily and directly. With these instruments, mistakes arising from faulty conversion of the measuring ranges or misreading the display are a thing of the past.

General ordering data

Version	Testing tools, Multimeter
Order No.	9423580000
Type	MULTIMETER 1037
GTIN (EAN)	4032248406142
Qty.	1 pc(s).

MULTIMETER 1037

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	66 mm	Depth (inches)	2.598 inch
Height	44 mm	Height (inches)	1.732 inch
Width	214.5 mm	Width (inches)	8.445 inch
Net weight	880 g		

Technical data

Description of article	Digital multimeter	Version	Multimeter + clamp-on meter
------------------------	--------------------	---------	-----------------------------

Measuring and testing devices

AC voltage measuring range	0.2 - 750 V	Battery type	9V block battery
DC voltage measuring range	0.2 - 1000 V	Display	digital
Frequency measurement	No	Frequency range, max.	500 Hz
Frequency range, min.	50 Hz	Measured capacitance value, max.	200 µF
Measured current value, max.	200 A	Measuring range category	CAT III
Opening width of current-measuring clamp-on attachment	23 mm	Resistance measuring range, max.	200 kΩ
Resistance measuring range, min.	0.2 Ω	Selection of measuring range	Manual
Test probe	Yes	Tested and approved according to	EN/IEC 61010-1
Working temperature, max.	50 °C	Working temperature, min.	0 °C

Classifications

ETIM 6.0	EC000069	ETIM 7.0	EC000069
ETIM 8.0	EC000069	ETIM 9.0	EC000069
ECLASS 9.0	27-20-03-01	ECLASS 9.1	27-20-03-08
ECLASS 10.0	27-20-03-01	ECLASS 11.0	27-20-03-01
ECLASS 12.0	27-20-03-01	ECLASS 13.0	27-20-03-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	

MULTIMETER 1037

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use



MULTIMETER 1037**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Accessories**

Accessories for testing and measuring equipment

**General ordering data**

Type	BLOCKBATTERIE 9V	Version
Order No.	9004810000	Testing tools, Battery
GTIN (EAN)	4008190050665	
Qty.	1 pc(s).	

Digital multimeters

Multimeters are capable of measuring a number of variables. Each instrument can measure voltage and resistance, as well as performing continuity and diode testing as standard.

In addition, the individual multimeters also feature extra measuring options such as current, frequency, capacitance and temperature. Digital multimeters have the advantage of a clear display which can be read easily and directly. With these instruments, mistakes arising from faulty conversion of the measuring ranges or misreading the display are a thing of the past.

General ordering data

Type	ZUB MULTI 1037	Version
Order No.	9205460000	Multimeter
GTIN (EAN)	4032248738731	
Qty.	1 pc(s).	