

**CLI C 2-4 GE/SW 6 MP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

**General ordering data**

|            |   |
|------------|---|
| Version    | CableLine, Conductor and cable markers, 4 - 10 mm, 4 x 7 mm, yellow |
| Order No.  | <a href="#">0251311520</a>  |
| Type       | CLI C 2-4 GE/SW 6 MP  |
| GTIN (EAN) | 4008190180614   |
| Qty.       | 100 pc(s).  |

## CLI C 2-4 GE/SW 6 MP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 8 mm   | Depth (inches)  | 0.315 inch |
| Height     | 4 mm   | Height (inches) | 0.157 inch |
| Width      | 7 mm   | Width (inches)  | 0.276 inch |
| Net weight | 0.16 g |                 |            |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

## General data

|  |  |                |
|--|--|----------------|
| Colour                                       | yellow   |                |
| Colour of printing                           | black  |                |
| Halogen                                      | Yes  |                |
| Insulation cross-section, max.               | 10   |                |
| Material                                     | PVC, soft, without Cadmium                     |                |
| Material colour according to resistance code | 4  |                |
| Number of markers per combination            | 1 Component part = Conductor and cable markers |                |
| Number of markers per packaging unit         | Form of supply                                 | Component part |
| Operating temperature range                  | -30...80 °C                                    |                |
| Operating temperature range, max.            | 80 °C  |                |
| Operating temperature range, min.            | -30 °C   |                |
| Orientation of print                         | horizontal                                     |                |
| Printed characters                           | Numbers  |                |
| Printing                                     | 6  |                |
| Printing method                              | hot-embossing                                  |                |
| Recommended industries                       | Process, Machinery                             |                |
| Type of printing                             | Standard                                       |                |
| UL 94 flammability rating                    | V-0  |                |
| Version                                      | MultiPack                                      |                |
| Width  | 7 mm   |                |

## Conductor and cable markers

|                               |                     |                                  |                          |
|-------------------------------|---------------------|----------------------------------|--------------------------|
| Conductor O.D.                | 4 - 10 mm           | Conductor O.D., max.             | 10 mm                    |
| Conductor O.D., min.          | 4 mm                | Conductor cross-section, max.    | 16 mm <sup>2</sup>       |
| Conductor cross-section, min. | 2.5 mm <sup>2</sup> | Cross-section for connected wire | 2.5 - 16 mm <sup>2</sup> |
| Halogen                       | Yes                 |                                  |                          |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ECLASS 9.0  | 27-40-04-01 | ECLASS 9.1  | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

## CLI C 2-4 GE/SW 6 MP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                             |  |
|-----------------------------|--|
| Product Change Notification | <a href="#">PCN CableLine_DE</a><br><a href="#">PCN CableLine_EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>                             |

### CLI C 2-4 GE/SW 6 MP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



Similar to illustration