

ZB 16/6K GE/GN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Bus bar taps with insulation offer finger safety on the one hand. On the other hand, the colored insulation also indicates the respective potential, such as the neutral conductor or PE.

General ordering data

Version	Clamping yoke (bus-bar), Clamping yoke, silver, Width: 10 mm, M 4, Steel
Order No.	0569660000
Type	ZB 16/6K GE/GN
GTIN (EAN)	4008190043681
Qty.	50 pc(s).

ZB 16/6K GE/GN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	30.7 mm	Depth (inches)	1.209 inch
Height	25 mm	Height (inches)	0.984 inch
Width	10 mm	Width (inches)	0.394 inch
Net weight	8.3 g		

Temperatures

Operating temperature range	For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity
-----------------------------	---

Material data

Material	Steel	Insulating material	PA
Colour	silver		

ZB 16/6K GE/GN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Rating data IECEx/ATEX

Certificate No. (ATEX)	DEMKO03ATEX136028U
Wire cross section max. (ATEX)	16 mm ²
Operating temperature range	For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity

Ex 2014/34/EU label

Certificate No. (IECEX)	IECEXULD13.0005U
Wire cross section max. (IECEX)	16 mm ²
Marking EN 60079-7	

Safety notice

Ex eb II C Gb

Installation instructions:
The potential equalisation (PE) rail modules are suitable for use in housings in atmospheres with flammable gases and dust. For use in areas with flammable gases, these housings must meet the requirements of EN 60079-0 and EN 60079-7. For use in areas with flammable dust, these housings must meet the requirements of EN 60079-0 and EN 60079-31.

When combined with other terminal block ranges and sizes, and when other accessories are used, you must comply with the clearance and creepage distances given.

Regarding accessory use, the manufacturer's instructions must be followed.

List of restrictions:
The PE rail modules are considered one component, with Ex marking when used with the busbar holders of type SH and WEW. When used independently, the above named components are not covered by this certificate.

II 2 G D

System specifications

Version	for busbar 6 x 6 mm
---------	---------------------

Additional technical data

Installation advice	Feed-through (bushing)	Type of mounting	when screwed in
---------------------	------------------------	------------------	-----------------

CSA rating data

Certificate No. (CSA)	12400-237	Wire cross section max. (CSA)	6 AWG
Wire cross section min. (CSA)	12 AWG		

ZB 16/6K GE/GN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Conductors for clamping (rated connection)**

Clamping screw	M 4	Connection cross-section, stranded, max.	25 mm ²
Connection cross-section, stranded, min.	16 mm ²	Stripping length	12 mm
Tightening torque, min.	2.6 Nm	Type of connection	Clamping yoke
Wire connection cross section, finely stranded, max.	16 mm ²	Wire connection cross section, finely stranded, min.	2.5 mm ²
Wire connection cross-section, solid core, max.	16 mm ²	Wire connection cross-section, solid core, min.	2.5 mm ²

General

Installation advice	Feed-through (bushing)
---------------------	------------------------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-46
ECLASS 12.0	27-14-11-46	ECLASS 13.0	27-25-01-16

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Attestation of Conformity UKCA Attestation of conformity ATEX Certificate IECEx Certificate UKCA Certificate
Engineering Data	CAD data – STEP
User Documentation	Installation Instruction Storage Conditions Terminal Blocks
Catalogues	Catalogues in PDF-format