

**CLI O 20-3 GE/SW B MP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

CLI O conductor markers are fitted to connected conductors, and are therefore suitable for updating existing systems. Without problems, three different sizes can be used for marking conductor cross-sections from 0.4 mm<sup>2</sup> to max. 4.0 mm<sup>2</sup>. The shape and design guarantee secure and permanent attachment of the individually combinable markers.

**Advantages:**

- Open markers for connected conductors
- Marker version with anti-rotation safeguard for secure combination marking
- Perfect for any supplementary labelling
- Extremely low space requirements
- Rapid clip-on attachment saves time

**General ordering data**

Version	CableLine, Conductor and cable markers, 3 - 4 mm, 3 x 5.5 mm, yellow
Order No.	<a href="#">0648101639</a>
Type	CLI O 20-3 GE/SW B MP
GTIN (EAN)	4008190010034
Qty.	200 pc(s).

## CLI O 20-3 GE/SW B MP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	5 mm	Depth (inches)	0.197 inch
Height	3 mm	Height (inches)	0.118 inch
Width	5.5 mm	Width (inches)	0.217 inch
Net weight	0.03 g		

## Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

## General data

Colour	yellow	Colour of printing	black
Halogen	Yes	Material	PVC, soft, without Cadmium
Material colour according to resistance code	4	Operating temperature range	-30...80 °C
Operating temperature range, max.	80 °C	Operating temperature range, min.	-30 °C
Orientation of print	horizontal	Printed characters	Upper-case letters
Printing	B	Printing method	hot-embossing
Recommended industries	Process, Machinery	Type of printing	Standard
UL 94 flammability rating	V-0	Version	MultiPack
Width	5.5 mm		

## Conductor and cable markers

Conductor O.D.	3 - 4 mm	Conductor O.D., max.	4 mm
Conductor O.D., min.	3 mm	Conductor cross-section, max.	3 mm <sup>2</sup>
Conductor cross-section, min.	1.5 mm <sup>2</sup>	Cross-section for connected wire	1.5 - 3 mm <sup>2</sup>
Halogen	Yes		

## Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

## Approvals

ROHS	Conform
------	---------

## Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

### CLI O 20-3 GE/SW B MP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



Similar to illustration