

ESG X20 MC NE WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|--------------------|--|
| Version | ESG, Device markers x 10 mm, PA 66, Colour: white, pluggable |
| Order No. | 1001140001 |
| Type | ESG X20 MC NE WS |
| GTIN (EAN) | 4032248692798 |
| Qty. | 1,120 pc(s). |
| compatible printer | 2715590000 2438520000 2438510000 |

ESG X20 MC NE WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 0.8 mm | Depth (inches) | 0.031 inch |
| Height | 2.5 mm | Height (inches) | 0.098 inch |
| Width | 10 mm | Width (inches) | 0.394 inch |
| Net weight | 0.08 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

General data

| | | |
|--|------------------------------|-----------|
| Application/manufacture | B&R X20 System | |
| Colour | white | |
| Halogen | No | |
| Material | PA 66 | |
| Material colour according to resistance code | 9 | |
| Number of markers per combination | 1 MultiCard = Device markers | |
| Number of markers per packaging unit | Form of supply | MultiCard |
| Operating temperature range | -40...100 °C | |
| Operating temperature range, max. | 100 °C | |
| Operating temperature range, min. | -40 °C | |
| UL 94 flammability rating | V-2 | |
| Version | pluggable | |
| Width | 10 mm | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ECLASS 9.0 | 27-40-06-29 | ECLASS 9.1 | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |
| ECLASS 14.0 | 27-28-11-04 | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|-----------------------------|--|
| Product Change Notification | Technical change to MultiCard material - DE Technical change to MultiCard material - EN MultiCard Material modification MultiCard Material Modifikation |
| Catalogues | Catalogues in PDF-format |

Creation date August 29, 2024 2:59:55 AM CEST

Catalogue status 17.08.2024 / We reserve the right to make technical changes.

ESG X20 MC NE WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

