

CLI O 10-3 GE NE MP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

CLI O conductor markers are fitted to connected conductors, and are therefore suitable for updating existing systems. Without problems, three different sizes can be used for marking conductor cross-sections from 0.4 mm² to max. 4.0 mm². The shape and design guarantee secure and permanent attachment of the individually combinable markers.

Advantages:

- Open markers for connected conductors
- Marker version with anti-rotation safeguard for secure combination marking
- Perfect for any supplementary labelling
- Extremely low space requirements
- Rapid clip-on attachment saves time

General ordering data

| | |
|------------|--|
| Version | CableLine, Conductor and cable markers, 2 - 3 mm, 3 x 4 mm, yellow |
| Order No. | 0689600000 |
| Type | CLI O 10-3 GE NE MP |
| GTIN (EAN) | 4008190104016 |
| Qty. | 200 pc(s). |

CLI O 10-3 GE NE MP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|--------|-----------------|------------|
| Depth | 4 mm | Depth (inches) | 0.157 inch |
| Height | 3 mm | Height (inches) | 0.118 inch |
| Width | 4 mm | Width (inches) | 0.157 inch |
| Net weight | 0.03 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

General data

| | | | |
|-----------------------------------|----------------------------|--|--------------------|
| Colour | yellow | Halogen | Yes |
| Material | PVC, soft, without Cadmium | Material colour according to resistance code | 4 |
| Operating temperature range | -30...80 °C | Operating temperature range, max. | 80 °C |
| Operating temperature range, min. | -30 °C | Printed characters | without |
| Printing | Blank | Recommended industries | Process, Machinery |
| Type of printing | neutral | UL 94 flammability rating | V-0 |
| Version | MultiPack | Width | 4 mm |

Conductor and cable markers

| | | | |
|-------------------------------|---------------------|----------------------------------|---------------------------|
| Conductor O.D. | 2 - 3 mm | Conductor O.D., max. | 3 mm |
| Conductor O.D., min. | 2 mm | Conductor cross-section, max. | 1.5 mm ² |
| Conductor cross-section, min. | 0.4 mm ² | Cross-section for connected wire | 0.4 - 1.5 mm ² |
| Halogen | Yes | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ECLASS 9.0 | 27-40-04-01 | ECLASS 9.1 | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

Environmental Product Compliance

| | |
|------------|---|
| REACH SVHC | / |
|------------|---|

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|

CLI O 10-3 GE NE MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



Similar to illustration