

VG PG21-MS54 ZR 10-19**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG MS ZR (standard brass cable gland, multiseal), Cable glands, PG 21, 7 mm, OD min. 10 - OD max. 19 mm, Brass, nickel-plated
Order No.	1009630000
Type	VG PG21-MS54 ZR 10-19
GTIN (EAN)	4032248714407
Qty.	25 pc(s).

VG PG21-MS54 ZR 10-19**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	29.5 mm	Length (inches)	1.161 inch
Net weight	45.92 g		

Temperatures

Operating temperature	-20 °C...80 °C
-----------------------	----------------

General information

AF size 1	28 mm	AF size 2	30 mm
Cable glands	PG	External thread	PG 21
Halogen	No	Length of thread	7 mm
Material	Brass, nickel-plated	Notch multi-layer sealing diameter 1	10 mm
Notch multi-layer sealing diameter 2	13 mm	Notch multi-layer sealing diameter 3	16 mm
Notch multi-layer sealing diameter 4	19 mm	Operating temperature range, max.	80 °C
Operating temperature range, min.	-20 °C	Outer cable diameter, max.	19 mm
Outer cable diameter, min.	10 mm	Protection degree	IP54
Seal insert	NBR	Torque for cap nut, max.	6.7 Nm
Torque for cap nut, min.	6.7 Nm	Torque for connecting adapter, max.	10 Nm
Torque for connecting adapter, min.	10 Nm		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-32
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-01	ECLASS 13.0	27-14-08-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--