

PTDS 4 DC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Power distribution using uncut cables with cross-sections from 1.5 to 6 mm².

Power supply / T-branch tap via PUSH IN connection (0.5 to 10 mm²) and/or plug-in connection (0.5 to 4 mm²).

Coloured markings provide clear assignment of wires.

- Power supply
- Power distribution
- Power branching

General ordering data

Version	Field Power® plug-in connector, DC, IP20, Polyamide, PUSH IN, Number of poles : 2 x 5
Order No.	1009990000
Type	PTDS 4 DC
GTIN (EAN)	4032248715244
Qty.	10 pc(s).

PTDS 4 DC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	36.15 mm	Depth (inches)	1.423 inch
Height	27.3 mm	Height (inches)	1.075 inch
Width	55.45 mm	Width (inches)	2.183 inch
Net weight	46.4 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...80 °C
---------------------	----------------	-----------------------	----------------

Approbations

Certificate No. (cURus)	E60693	Institute (cURus)	CURUS
-------------------------	--------	-------------------	-------

Clamping capacity, PUSH IN connection

Blade size, PUSH IN connection	3.0 x 0.5 mm	Clamping range, max. PUSH IN connection	4 mm ²
Clamping range, min. PUSH IN connection	0.5 mm ²	Cross-section for connected wire PUSH IN connection, solid, min.	0.5 mm ²
Cross-section for connected wire, PUSH IN connection, solid, max.	4 mm ²	Cross-section for connected wire, flexible with wire-end ferrules, 12mm with plastic collar, DIN 46228/1, PUSH IN connection, max.	4 mm ²
Cross-section for connected wire, flexible with wire-end ferrules, 12mm with plastic collar, DIN 46228/1, PUSH IN connection, min.	0.5 mm ²	Cross-section for connected wire, flexible with wire-end ferrules, 12mm with plastic collar, DIN 46228/4, PUSH IN connection, max.	4 mm ²
Cross-section for connected wire, flexible with wire-end ferrules, 12mm with plastic collar, DIN 46228/4, PUSH IN connection, min.	0.5 mm ²	Cross-section for connected wire, flexible with wire-end ferrules, 8mm with plastic collar, DIN 46228/1, PUSH IN connection, max.	4 mm ²
Cross-section for connected wire, flexible with wire-end ferrules, 8mm with plastic collar, DIN 46228/1, PUSH IN connection, min.	0.5 mm ²	Cross-section for connected wire, flexible with wire-end ferrules, 8mm with plastic collar, DIN 46228/4, PUSH IN connection, max.	4 mm ²
Cross-section for connected wire, flexible with wire-end ferrules, 8mm with plastic collar, DIN 46228/4, PUSH IN connection, min.	0.5 mm ²	Cross-section for connected wire, flexible, PUSH IN connection, max.	4 mm ²
Cross-section for connected wire, flexible, PUSH IN connection, min.	0.5 mm ²	Finely-stranded flexible, max. PUSH IN connection	4 mm ²
Finely-stranded flexible, min. PUSH IN connection	0.5 mm ²	Stripping length, PUSH IN connection	12 mm
Wire connection cross section, stranded, PUSH IN connection, max.	4 mm ²	Wire connection cross section, stranded, PUSH IN connection, min.	0.5 mm ²

PTDS 4 DC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Clamping capacity

Connection data - plug-in connector	Wire connection method		PUSH IN
	Blade size of operating tool		3.0 x 0.5 mm
	Stripping length		12 mm
	Number of poles		5
	Conductor connection cross-section, solid, max.		4 mm ²
	Conductor connection cross-section, solid, min.		0.5 mm ²
	Conductor connection cross-section, stranded, max.		4 mm ²
	Conductor connection cross-section, stranded, min.		0.5 mm ²
	Conductor connection cross-section, finely stranded, max.		4 mm ²
	Conductor connection cross-section, finely stranded, min.		0.5 mm ²
	Conductor connection cross-section, finest stranded, max.		4 mm ²
	Conductor connection cross-section, finest stranded, min.		0.5 mm ²
	Conductor connection cross-section with wire end ferrule	Type of wire end ferrule	12 mm with plastic collar
		Standard	DIN 46228/1
		Cross-section, min.	0.5 mm ²
		Cross-section, max.	4 mm ²
		Type of wire end ferrule	12 mm with plastic collar
		Standard	DIN 46228/4
		Cross-section, min.	0.5 mm ²
		Cross-section, max.	4 mm ²
		Type of wire end ferrule	8 mm with plastic collar
		Standard	DIN 46228/1
		Cross-section, min.	0.5 mm ²
		Cross-section, max.	4 mm ²
		Type of wire end ferrule	8 mm with plastic collar
		Standard	DIN 46228/4
		Cross-section, min.	0.5 mm ²
		Cross-section, max.	4 mm ²
		Type of wire end ferrule	Twin wire-end ferrules
		Cross-section, min.	0.5 mm ²
		Cross-section, max.	4 mm ²

General data

Insulating material	Polyamide	Silicone	No
Colour	black	Protection degree	IP20
UL 94 flammability rating	V-0	Type of mounting	Plugged
Can be coded	Yes, Coded on PE	Test point	2 mm
Voltage type	DC	Number of poles	2 x 5
Number of connections / pole	2	Wire connection method	PUSH IN
Conductor outlet direction	90°		

PTDS 4 DC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Rated data acc. to IEC

Rated data acc. to IEC for plug-in connector

Voltage type	DC
Standard	IEC 60947-7-1, IEC 60947-7-2, IEC 61984
Rated voltage	690 V
Rated impulse withstand voltage	8 kV
Rated current (3 loaded poles)	32 A
Rated current (4 loaded poles)	25 A

Rated data acc. to UL

Rated data acc. to UL for plug-in connector

Standard	UL 1059
Note	for use with UL-listed TC-ER cables
Conductor connection cross-section, AWG, max.	AWG 12
Conductor connection cross-section, AWG, min.	AWG 16
Rated voltage	600 V
Rated current	20 A

Classifications

ETIM 6.0	EC002943	ETIM 7.0	EC002943
ETIM 8.0	EC002943	ETIM 9.0	EC002943
ECLASS 9.0	27-44-02-92	ECLASS 9.1	27-44-03-90
ECLASS 10.0	27-44-02-92	ECLASS 11.0	27-44-02-92
ECLASS 12.0	27-44-02-92	ECLASS 13.0	27-44-02-92

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E60693

Downloads


Approval/Certificate/Document of Conformity	UL Certificate FieldPower® terminals and plug-in connectors
Engineering Data	Manufacturer's Declaration FieldPower® plug-in connectors and HQ adapters
User Documentation	CAD data – STEP
Catalogues	Manual FieldPower® PTS 4 and PTDS 4
	Catalogues in PDF-format

PTDS 4 DC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



PTDS 4 DC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	WS 12/6 MC NE WS	Version
Order No.	1609900000	WS, Terminal marker, 12 x 6 mm, Pitch in mm (P): 6.00 Weidmueller,
GTIN (EAN)	4008190203467	Allen-Bradley, white
Qty.	600 pc(s).	

Locking elements



The plugs can be securely and easily fixed to the base terminal by using a locking element. The locking element avoids an unintentional disconnection of the plugs from the base terminal and ensures maximum safety.

General ordering data

Type	ZVR ZP2.5	Version
Order No.	1816130000	Z-series, Locking clips, yellow, 3.9 mm
GTIN (EAN)	4032248370702	
Qty.	25 pc(s).	

PTDS 4 DC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Slotted screwdriver**

Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

General ordering data

Type	SDS 0.5X3.0X80	Version
Order No.	2749330000	Screwdriver, Blade width (B): 3 mm, Blade length: 80 mm, Blade
GTIN (EAN)	4050118895551	thickness (A): 0.5 mm
Qty.	1 pc(s).	

Tools

Sheathing stripper for PVC cables

**General ordering data**

Type	AM 16	Version
Order No.	9204190000	Tools, Sheathing strippers
GTIN (EAN)	4032248608133	
Qty.	1 pc(s).	
Type	AM 25	Version
Order No.	9001540000	Tools, Sheathing strippers
GTIN (EAN)	4008190138271	
Qty.	1 pc(s).	