

PTS 4 MPB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Power distribution using uncut cables with cross-sections from 1.5 to 6 mm².

Power supply / T-branch tap via PUSH IN connection (0.5 to 10 mm²) and/or plug-in connection (0.5 to 4 mm²).

Coloured markings provide clear assignment of wires.

- Power supply
- Power distribution
- Power branching

General ordering data

Version	Field Power® plug-in connector, IP20, Polyamide, PUSH IN, Number of poles : 5
Order No.	1010910000
Type	PTS 4 MPB
GTIN (EAN)	4032248717330
Qty.	10 pc(s).

PTS 4 MPB

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	36.15 mm	Depth (inches)	1.423 inch
Height	27.3 mm	Height (inches)	1.075 inch
Width	55.45 mm	Width (inches)	2.183 inch
Net weight	3.8 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...80 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Approbations

Certificate No. (cURus)	E60693	Institute (cURus)	CURUS
-------------------------	--------	-------------------	-------

Clamping capacity, PUSH IN connection

Blade size, PUSH IN connection	3.0 x 0.5 mm	Clamping range, max. PUSH IN connection	4 mm ²
Clamping range, min. PUSH IN connection	0.5 mm ²	Cross-section for connected wire PUSH IN connection, solid, min.	0.5 mm ²
Cross-section for connected wire, PUSH IN connection, solid, max.	4 mm ²	Cross-section for connected wire, flexible with wire-end ferrules, 12mm with plastic collar, DIN 46228/1, PUSH IN connection, max.	4 mm ²
Cross-section for connected wire, flexible with wire-end ferrules, 12mm with plastic collar, DIN 46228/1, PUSH IN connection, min.	0.5 mm ²	Cross-section for connected wire, flexible with wire-end ferrules, 12mm with plastic collar, DIN 46228/4, PUSH IN connection, max.	4 mm ²
Cross-section for connected wire, flexible with wire-end ferrules, 12mm with plastic collar, DIN 46228/4, PUSH IN connection, min.	0.5 mm ²	Cross-section for connected wire, flexible with wire-end ferrules, 8mm with plastic collar, DIN 46228/1, PUSH IN connection, max.	4 mm ²
Cross-section for connected wire, flexible with wire-end ferrules, 8mm with plastic collar, DIN 46228/1, PUSH IN connection, min.	0.5 mm ²	Cross-section for connected wire, flexible with wire-end ferrules, 8mm with plastic collar, DIN 46228/4, PUSH IN connection, max.	4 mm ²
Cross-section for connected wire, flexible with wire-end ferrules, 8mm with plastic collar, DIN 46228/4, PUSH IN connection, min.	0.5 mm ²	Cross-section for connected wire, flexible, PUSH IN connection, max.	4 mm ²
Cross-section for connected wire, flexible, PUSH IN connection, min.	0.5 mm ²	Finely-stranded flexible, max. PUSH IN connection	4 mm ²
Finely-stranded flexible, min. PUSH IN connection	0.5 mm ²	Number of poles	5
Stripping length, PUSH IN connection	12 mm	Wire connection cross section, stranded, PUSH IN connection, max.	4 mm ²
Wire connection cross section, stranded, PUSH IN connection, min.	0.5 mm ²		

PTS 4 MPB

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Clamping capacity

Connection data - plug-in connector	Wire connection method	PUSH IN	
	Blade size of operating tool	3.0 x 0.5 mm	
	Stripping length	12 mm	
	Number of poles	5	
	Conductor connection cross-section, solid, max.	4 mm ²	
	Conductor connection cross-section, solid, min.	0.5 mm ²	
	Conductor connection cross-section, stranded, max.	4 mm ²	
	Conductor connection cross-section, stranded, min.	0.5 mm ²	
	Conductor connection cross-section, finely stranded, max.	4 mm ²	
	Conductor connection cross-section, finely stranded, min.	0.5 mm ²	
	Conductor connection cross-section, finest stranded, max.	4 mm ²	
	Conductor connection cross-section, finest stranded, min.	0.5 mm ²	
	Conductor connection cross-section with wire end ferrule	Type of wire end ferrule	12 mm with plastic collar
		Standard	DIN 46228/1
		Cross-section, min.	0.5 mm ²
		Cross-section, max.	4 mm ²
		Type of wire end ferrule	12 mm with plastic collar
		Standard	DIN 46228/4
		Cross-section, min.	0.5 mm ²
		Cross-section, max.	4 mm ²
Type of wire end ferrule		8 mm with plastic collar	
Standard		DIN 46228/1	
Cross-section, min.		0.5 mm ²	
Cross-section, max.		4 mm ²	
Type of wire end ferrule		8 mm with plastic collar	
Standard		DIN 46228/4	
Cross-section, min.		0.5 mm ²	
Cross-section, max.		4 mm ²	
Type of wire end ferrule	Twin wire-end ferrules		
Cross-section, min.	0.5 mm ²		
Cross-section, max.	4 mm ²		

General data

Insulating material	Polyamide	Silicone	No
Colour	black	Protection degree	IP20
UL 94 flammability rating	V-0	Type of mounting	Plugged
Can be coded	Yes, Coded on PE	Test point	2 mm
Number of poles	5	Number of connections / pole	1
Wire connection method	PUSH IN	Conductor outlet direction	90°

PTS 4 MPB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Rated data acc. to IEC

Rated data acc. to IEC for plug-in connector	Standard	IEC 60947-7-1, IEC 60947-7-2, IEC 61984
	Rated voltage	690 V
	Rated impulse withstand voltage	8 kV
	Rated current (3 loaded poles)	32 A
	Rated current (4 loaded poles)	25 A

Rated data acc. to UL

Rated data acc. to UL for plug-in connector	Standard	UL 1059
	Note	for use with UL-listed TC-ER cables
	Conductor connection cross-section, AWG, max.	AWG 12
	Conductor connection cross-section, AWG, min.	AWG 16
	Rated voltage	600 V
	Rated current	20 A

Classifications

ETIM 6.0	EC002943	ETIM 7.0	EC002943
ETIM 8.0	EC002943	ETIM 9.0	EC002943
ECLASS 9.0	27-44-02-92	ECLASS 9.1	27-44-03-90
ECLASS 10.0	27-44-02-92	ECLASS 11.0	27-44-02-92
ECLASS 12.0	27-44-02-92	ECLASS 13.0	27-44-02-92

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E60693

Downloads

Approval/Certificate/Document of Conformity	UL Certificate FieldPower® terminals and plug-in connectors Manufacturer's Declaration FieldPower® plug-in connectors and HQ adapters
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

Data sheet

PTS 4 MPB

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

