

SFC 3/21 MC NE RT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



The SlimFix Clip combines two advantages: its unique closure mechanism offers the reliability of a closed marker with the ease of installation of an open marker. The clip mechanism allows quick and convenient installation of the marker even after the conductor has been installed. SlimFix Clips are suitable for conductors and cables with an outside diameter of up to 5 mm. The large marking surface - up to 30 mm - enables long character strings. The material is halogen-free and complies with flammability rating V2.

Advantages:

- Halogen-free material
- Flammability rating V2
- Fast installation without tools
- Markers in proven MultiCard format
- Available in the heights of 12 mm, 21 mm and 30 mm

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	SlimFix Clip, Conductor and cable markers, 3.5 - 7 mm, 21 x 12.5 mm, red
Order No.	1025290000
Type	SFC 3/21 MC NE RT
GTIN (EAN)	4032248746347
Qty.	80 pc(s).
compatible printer	2715590000 2438520000 2438510000

SFC 3/21 MC NE RT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	11.3 mm	Depth (inches)	0.445 inch
Height	21 mm	Height (inches)	0.827 inch
Width	12.5 mm	Width (inches)	0.492 inch
Net weight	1.338 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

General data

Colour	red	
Halogen	No	
Material	Polyamide 66	
Material colour according to resistance code	2	
Number of markers per combination	1 MultiCard = Conductor and cable markers	
Number of markers per packaging unit	Form of supply	MultiCard
Operating temperature range	-40...100 °C	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Recommended industries	Machinery	
Size of labelling field	21 x 5 mm	
Type of printing	neutral	
UL 94 flammability rating	V-2	
Width	12.5 mm	

Conductor and cable markers

Conductor O.D.	3.5 - 7 mm	Conductor O.D., max.	7 mm
Conductor O.D., min.	3.5 mm	Conductor cross-section, max.	10 mm ²
Conductor cross-section, min.	4 mm ²	Cross-section for connected wire	4 - 10 mm ²
Halogen	No		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

SFC 3/21 MC NE RT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
Product Change Notification	Technical change - DE Technical change - EN MultiCard Material modification MultiCard Material Modifikation
Catalogues	Catalogues in PDF-format
Brochures	

SFC 3/21 MC NE RT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

