

SAIB-5/9-ZF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

Tension-clamp connection delivers excellent functional security and reduced installation times. With this technology the conductor is plugged into the tension clamp without a wire-end ferrule (optionally with wire-end ferrule). The connection between the conductor and tension clamp is vibration-resistant and boasts long-term stability.

General ordering data

Version	Field attachable connector, M12, Female socket, straight
Order No.	1044710000
Type	SAIB-5/9-ZF
GTIN (EAN)	4032248777167
Qty.	1 pc(s).

SAIB-5/9-ZF

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	25 g
------------	------

Technical data customisable plug-in connectors

Cable diameter	4...6 mm (PG7)/ 6...8 mm (PG9)	Cable diameter, max.	8 mm
Cable diameter, min.	6 mm	Coding	A-coded
Conductor cross-section, max.	0.5 mm ²	Conductor cross-section, min.	0.14 mm ²
Contact surface	Gold-plated	Housing main material	PA
Insulation strength	10 ⁸ Ω	Number of poles	5
Plugging cycles	≥ 100	Pollution severity	3
Protection degree	IP67	Rated current	4 A
Rated voltage	60 V	Shield connection	No
Temperature range of housing	-40 ... +85 °C	Threaded ring material	Diecast zinc
Type of connection	Tension-clamp connection		

General Info

Number of poles	5	Connection 1	M12
Connection 2	Tension-clamp	Housing main material	PA
Connection thread	M12	Contact surface	Gold-plated
Protection degree	IP67	Plugging cycles	≥ 100

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ECLASS 9.0	27-44-01-02	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-02	ECLASS 11.0	27-44-01-02
ECLASS 12.0	27-44-01-16	ECLASS 13.0	27-44-01-02
ECLASS 14.0	27-44-01-16		

Environmental Product Compliance

REACH SVHC	Imidazolidine-2-thione 96-45-7
SCIP	a2cb82cf-1eab-43cd-bafb-63d26622fe9e
RoHS Compliance Status	Compliant without exemption

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

Creation date August 29, 2024 10:50:18 PM CEST

Catalogue status 17.08.2024 / We reserve the right to make technical changes.

SAIB-5/9-ZF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Pole scheme

