

ELS 7/40 MC NE GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

ELS MultiCard markers can be printed with a PrintJet, plotter or SMark printer. In particular, colour printing with PrintJet AVANCED allows the eye-catching identification marking of cables and terminal strips in many ways.

ELS 6/30 for use in the WKM 8/30 cable markers or in the EM8/30 group-tag carriers

ELS 7/40 for use in the SchT5S group-tag carriers

ELS 16/40 for use in the WKM 18/43 cable markers or the SchT5 group-tag carriers

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	ELS, Insert markers, 40 x 7 mm, yellow
Order No.	1045650000
Type	ELS 7/40 MC NE GE
GTIN (EAN)	4032248779635
Qty.	40 pc(s).
compatible printer	2715590000 2438520000 2438510000

ELS 7/40 MC NE GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	1 mm	Depth (inches)	0.039 inch
Height	40 mm	Height (inches)	1.575 inch
Width	7 mm	Width (inches)	0.276 inch
Net weight	2.175 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

General data

Colour	yellow	
Halogen	No	
Material	Polyamide 66	
Material colour according to resistance code	4	
Number of markers per combination	1 MultiCard = Insert markers	
Number of markers per packaging unit	Form of supply	MultiCard
Number per sheet	8	
Operating temperature range	-40...100 °C	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
UL 94 flammability rating	V-2	
Width	7 mm	

Conductor and cable markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
Product Change Notification	MultiCard Material modification MultiCard Material Modifikation
Catalogues	Catalogues in PDF-format

ELS 7/40 MC NE GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings




ELS 7/40 MC NE GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****SchT group marker carrier**

The SchT 5 S group tag carriers are clipped directly onto the TS 32 mounting rail (G-rail) or the TS 35 mounting rail (top-hat rail). It is therefore possible to label the terminal strip irrespective of the terminal and the type of terminal. SchT 5 and SchT 5 S are fitted with ESO 5, STR 5 protective strips.

The SchT 7 is a hinged group tag carrier for inlay tags which enables easy access to the clamping screw.

The SchT 7 is fitted with ESO 7, STR 7 protective strips or DEK 5.

Inlay tags and protective strips can be found under "Accessories".

General ordering data

Type	SCHT 5 S V0	Version
Order No.	1762370000	SCHT, Terminal marker, 44.5 x 9.5 mm, Pitch in mm (P): 5.00 beige
GTIN (EAN)	4032248043842	
Qty.	20 pc(s).	
Type	SCHT 5 S	Version
Order No.	1631930000	SCHT, Terminal marker, 44.5 x 9.5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190206680	Weidmueller, beige
Qty.	20 pc(s).	
Type	SCHT 5 S GR	Version
Order No.	1461730000	SCHT, Terminal marker, 44.5 x 9.5 mm, Pitch in mm (P): 5.00 grey
GTIN (EAN)	4050118267709	
Qty.	20 pc(s).	