

ELS 16/40 MC SDR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



ELS MultiCard markers can be printed with a PrintJet, plotter or SMark printer. In particular, colour printing with PrintJet AVANCED allows the eye-catching identification marking of cables and terminal strips in many ways.

ELS 6/30 for use in the WKM 8/30 cable markers or in the EM8/30 group-tag carriers

ELS 7/40 for use in the SchT5S group-tag carriers

ELS 16/40 for use in the WKM 18/43 cable markers or the SchT5 group-tag carriers

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|--------------------|--|
| Version | ELS, Insert markers, 40 x 16 mm, To customer specification |
| Order No. | 1045690000 |
| Type | ELS 16/40 MC SDR |
| GTIN (EAN) | 4032248779666 |
| Qty. | 8 pc(s). |
| compatible printer | 2715590000 2438520000 2438510000 |

ELS 16/40 MC SDR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|--------|-----------------|------------|
| Depth | 1 mm | Depth (inches) | 0.039 inch |
| Height | 40 mm | Height (inches) | 1.575 inch |
| Width | 16 mm | Width (inches) | 0.63 inch |
| Net weight | 1.77 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

General data

| | | |
|--------------------------------------|---|-----------|
| Colour | To customer specification | |
| Colour of printing | black | |
| Halogen | No | |
| Material | Polyamide 66 | |
| Number of markers per combination | 1 MultiCard = Insert markers | |
| Number of markers per packaging unit | Form of supply | MultiCard |
| Number per sheet | 8 | |
| Operating temperature range | -40... 100 °C | |
| Operating temperature range, max. | 100 °C | |
| Operating temperature range, min. | -40 °C | |
| Printed characters | Based on customer requirements (Please send M-Print PRO file) | |
| Printing method | MC Laser | |
| UL 94 flammability rating | V-2 | |
| Width | 16 mm | |

Conductor and cable markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ECLASS 9.0 | 27-40-04-01 | ECLASS 9.1 | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |
| ECLASS 14.0 | 27-28-11-02 | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|

ELS 16/40 MC SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

SchT group marker carrier



The SchT 5 S group tag carriers are clipped directly onto the TS 32 mounting rail (G-rail) or the TS 35 mounting rail (top-hat rail). It is therefore possible to label the terminal strip irrespective of the terminal and the type of terminal. SchT 5 and SchT 5 S are fitted with ESO 5, STR 5 protective strips.

The SchT 7 is a hinged group tag carrier for inlay tags which enables easy access to the clamping screw. The SchT 7 is fitted with ESO 7, STR 7 protective strips or DEK 5.

Inlay tags and protective strips can be found under "Accessories".

General ordering data

| Type | Version |
|--------------------------------------|--|
| SCHT 5 VO | SCHT, Terminal marker, 44.5 x 19.5 mm, Pitch in mm (P): 5.00 beige |
| Order No. 1762360000 | |
| GTIN (EAN) 4032248043835 | |
| Qty. 20 pc(s). | |

| Type | Version |
|--------------------------------------|--|
| SCHT 5 | SCHT, Terminal marker, 44.5 x 19.5 mm, Pitch in mm (P): 5.00 |
| Order No. 0292460000 | Weidmueller, beige |
| GTIN (EAN) 4008190105440 | |
| Qty. 20 pc(s). | |

WKM for inlay tags



The halogen-free, transparent pocket of the WKM offers outstanding protection against environmental influences. Thanks to firm fixation with cable ties, it is suitable for almost all wire cross-sections.

The pre-printed tags are simply inserted into the WKM holder and secured with a clip. WKM cable markers are the right solution for maximum efficiency in on-site marking.

Your advantage when using WKM cables

- Paper and polyester labels can be printed individually with conventional office printers
- The robust design in combination with MultiCard ELS tags guarantees maximum protection against environmental influences

General ordering data

| Type | Version |
|--------------------------------------|--|
| WKM 18/43 | WKM, Conductor and cable markers, 7 - 115 mm, 43 x 18 mm, Wire |
| Order No. 1610700000 | and cable markers, Transparent |
| GTIN (EAN) 4008190204488 | |
| Qty. 50 pc(s). | |