


THM MT30X 101/74 GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

General ordering data

| | |
|--------------------|---|
| Version | THM, Device markers, 74 x 101 mm, yellow |
| Order No. | 1061810000 |
| Type | THM MT30X 101/74 GE |
| GTIN (EAN) | 4032248814220 |
| Qty. | 1 pc(s). |
| compatible printer | 2599430000 2599440000 |

THM MT30X 101/74 GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Depth | 0.08 mm | Depth (inches) | 0.003 inch |
| Height | 74 mm | Height (inches) | 2.913 inch |
| Width | 101 mm | Width (inches) | 3.976 inch |
| Net weight | 640 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

General data

| | | |
|--------------------------------------|-------------------------------|------------|
| Adhesive | Acrylate | |
| Colour | yellow | |
| Halogen | No | |
| Material | Polyester | |
| Number of markers per combination | 1 Label reel = Device markers | |
| Number of markers per packaging unit | Form of supply | Label reel |
| Number per roll | 500 | |
| Operating temperature range | -40...150 °C | |
| Operating temperature range, max. | 150 °C | |
| Operating temperature range, min. | -40 °C | |
| Printing method | Thermal transfer | |
| UL 94 flammability rating | V-0 | |
| Version | Self-adhesive, halogen-free | |
| Width | 101 mm | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ECLASS 9.0 | 27-40-06-29 | ECLASS 9.1 | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads


| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |

THM MT30X 101/74 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



THM MT30X 101/74 GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | |
|------------|----------------------------|------------|
| Type | RIBBON MM 110/360 SW | Version |
| Order No. | 2005070000 | Ink ribbon |
| GTIN (EAN) | 4050118390049 | |
| Qty. | 1 pc(s). | |