

SFC 2.5/21 MC SDR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



The SlimFix Clip combines two advantages: its unique closure mechanism offers the reliability of a closed marker with the ease of installation of an open marker. The clip mechanism allows quick and convenient installation of the marker even after the conductor has been installed. SlimFix Clips are suitable for conductors and cables with an outside diameter of up to 5 mm. The large marking surface - up to 30 mm - enables long character strings. The material is halogen-free and complies with flammability rating V2.

Advantages:

- Halogen-free material
- Flammability rating V2
- Fast installation without tools
- Markers in proven MultiCard format
- Available in the heights of 12 mm, 21 mm and 30 mm

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|--------------------|---|
| Version | SlimFix Clip, Conductor and cable markers, 4 - 6 mm, 21 x 9.3 mm, To customer specification |
| Order No. | 1062110000 |
| Type | SFC 2.5/21 MC SDR |
| GTIN (EAN) | 4032248811823 |
| Qty. | 24 pc(s). |
| compatible printer | 2715590000 2438520000 2438510000 |

SFC 2.5/21 MC SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 9.1 mm | Depth (inches) | 0.358 inch |
| Height | 21 mm | Height (inches) | 0.827 inch |
| Width | 9.3 mm | Width (inches) | 0.366 inch |
| Net weight | 0.933 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

General data

| | | |
|--------------------------------------|--|-----------|
| Advice label | Colour based on customer requirements (Please send M-Print PRO file) | |
| Colour | To customer specification | |
| Colour of printing | black | |
| Halogen | No | |
| Material | Polyamide 66 | |
| Number of markers per combination | 1 MultiCard = Conductor and cable markers | |
| Number of markers per packaging unit | Form of supply | MultiCard |
| Operating temperature range | -40...100 °C | |
| Operating temperature range, max. | 100 °C | |
| Operating temperature range, min. | -40 °C | |
| Orientation of print | horizontal | |
| Printed characters | Based on customer requirements (Please send M-Print PRO file) | |
| Printing method | MC Laser | |
| Size of labelling field | 21 x 5.8 mm | |
| Type of printing | To customer specification | |
| UL 94 flammability rating | V-2 | |
| Width | 9.3 mm | |

Conductor and cable markers

| | | | |
|-------------------------------|-------------------|----------------------------------|------------------------|
| Conductor O.D. | 4 - 6 mm | Conductor O.D., max. | 6 mm |
| Conductor O.D., min. | 4 mm | Conductor cross-section, max. | 10 mm ² |
| Conductor cross-section, min. | 4 mm ² | Cross-section for connected wire | 4 - 10 mm ² |
| Halogen | No | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ECLASS 9.0 | 27-40-04-01 | ECLASS 9.1 | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
| Brochures | |