


WSH 1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	Accessories, Rail support, PA 66 GF 30
Order No.	1068700000
Type	WSH 1
GTIN (EAN)	4008190118389
Qty.	10 pc(s).

WSH 1

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	57 mm	Depth (inches)	2.244 inch
Height	110 mm	Height (inches)	4.331 inch
Width	8 mm	Width (inches)	0.315 inch
Net weight	26.175 g		

Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-50 °C...65 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Material data

Material	PA 66 GF 30	Colour	dark beige
UL 94 flammability rating	HB		

System specifications

Version	For the mounting rails	Rail	TS 35
---------	------------------------	------	-------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in	Type of mounting	when screwed in

Dimensions

Pitch in mm (P)	8 mm	Mounting offset	66 mm
-----------------	------	-----------------	-------

General

Installation advice	Direct mounting	Number of poles	1
Rail	TS 35		

Classifications

ETIM 6.0	EC001166	ETIM 7.0	EC001166
ETIM 8.0	EC001166	ETIM 9.0	EC001166
ECLASS 9.0	27-40-06-07	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-40-06-07	ECLASS 11.0	27-40-06-07
ECLASS 12.0	27-40-06-07	ECLASS 13.0	27-40-06-07
ECLASS 14.0	27-40-06-07		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

WSH 1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

WSH 1

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Copper



Of all the metals used, copper has the best electrical conductivity, which results in the highest short-circuit resistance. This makes the copper busbar the most widely used variant.

General ordering data

Type	SSCH 10X3X1000 CU/SN	Version
Order No.	0348900000	Busbar (terminal), silver, Height: 1000 mm, Depth: 3 mm, Copper
GTIN (EAN)	4008190024802	
Qty.	1 m	

Brass



Brass bus bars, as a copper alloy, has positive properties in terms of electrical conductivity and at the same time has a higher strength than copper against mechanical stress.

General ordering data

Type	SA 3.00X10.00X1000 CUZN ...	Version
Order No.	0259800000	Busbar (terminal), silver, Height: 1000 mm, Depth: 3 mm, Brass
GTIN (EAN)	4008190049300	
Qty.	1 m	

WSH 1

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Steel



Steel bus bars, together with stainless steel, have the highest strength among metallic busbars and are used in applications where short-circuit resistance plays only a secondary role.

General ordering data

Type	SSCH 10X3X1000 ST/ZN	Version
Order No.	0438000000	Busbar (terminal), silver, Height: 1000 mm, Depth: 3 mm, Steel
GTIN (EAN)	4008190080938	
Qty.	1 m	