

**SFX 30/60 MC NE GR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration



SlimFix X are halogen-free conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. SlimFix is an acknowledged and approved marker type in traffic engineering. The SF tool allows easy installation even in case of small markers.

- Halogen-free material
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm<sup>2</sup>
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|                    |  |
|--------------------|--|
| Version            | SlimFix X, Conductor and cable markers, 7 - 40 mm, 60 x 30 mm, grey              |
| Order No.          | <a href="#">1083250000</a>   |
| Type               | SFX 30/60 MC NE GR   |
| GTIN (EAN)         | 4032248847389  |
| Qty.               | 30 pc(s).  |
| compatible printer | <a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a> |

## SFX 30/60 MC NE GR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 1.2 mm  | Depth (inches)  | 0.047 inch |
| Height     | 60 mm   | Height (inches) | 2.362 inch |
| Width      | 30 mm   | Width (inches)  | 1.181 inch |
| Net weight | 4.533 g |                 |            |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

## General data

|  |   |           |
|--|---|-----------|
| Colour                                       | grey                                      |           |
| Halogen                                      | No  |           |
| Material                                     | Polyamide 66                              |           |
| Material colour according to resistance code | 8   |           |
| Number of markers per combination            | 1 MultiCard = Conductor and cable markers |           |
| Number of markers per packaging unit         | Form of supply                            | MultiCard |
| Operating temperature range                  | -40...100 °C                              |           |
| Operating temperature range, max.            | 100 °C                                    |           |
| Operating temperature range, min.            | -40 °C                                    |           |
| Recommended industries                       | Transportation, Machinery                 |           |
| Size of labelling field                      | 45 x 30 mm                                |           |
| Type of printing                             | neutral                                   |           |
| UL 94 flammability rating                    | V-2                                       |           |
| Version                                      | Installation with cable ties              |           |
| Width  | 30 mm                                     |           |

## Conductor and cable markers

|                               |                    |                                  |                          |
|-------------------------------|--------------------|----------------------------------|--------------------------|
| Conductor O.D.                | 7 - 40 mm          | Conductor O.D., max.             | 40 mm                    |
| Conductor O.D., min.          | 7 mm               | Conductor cross-section, max.    | 500 mm <sup>2</sup>      |
| Conductor cross-section, min. | 16 mm <sup>2</sup> | Cross-section for connected wire | 16 - 500 mm <sup>2</sup> |
| Halogen                       | No                 |                                  |                          |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ECLASS 9.0  | 27-40-04-01 | ECLASS 9.1  | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                             |  |
|-----------------------------|--|
| Engineering Data            | <a href="#">CAD data – STEP</a>  |
| Engineering Data            | <a href="#">Zuken E3.S</a>   |
| Product Change Notification | <a href="#">MultiCard Material modification</a><br><a href="#">MultiCard Material Modifikation</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>   |

Creation date June 1, 2024 1:31:07 PM CEST

Catalogue status 18.05.2024 / We reserve the right to make technical changes.

### SFX 30/60 MC NE GR

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

