

**THM WO 24.5/62 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

**General ordering data**

Version	THM, Conductor and cable markers, 6.1 - 13.7 mm, 24.5 x 62 mm, white
Order No.	<a href="#">1109130000</a>
Type	THM WO 24.5/62 WS
GTIN (EAN)	4032248885534
Qty.	1 pc(s).
compatible printer	<a href="#">2599430000</a> <a href="#">2599440000</a>

## THM WO 24.5/62 WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	24.5 mm	Height (inches)	0.965 inch
Width	62 mm	Width (inches)	2.441 inch
Net weight	557 g		

## Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

## General data

Adhesive	Polyacrylate adhesive	
Approval acc. to UL 969	Yes	
Colour	white	
Halogen	No	
Material	Polyester film	
Material colour according to resistance code	9	
Number of markers per combination	1 Label reel = Conductor and cable markers	
Number of markers per packaging unit	Form of supply	Label reel
Number per roll	2,500	
Operating temperature range	-40...150 °C	
Operating temperature range, max.	150 °C	
Operating temperature range, min.	-40 °C	
Size of labelling field	19.05 x 24.5 mm	
Type of printing	neutral	
UL 94 flammability rating	V-0	
Version	Self-adhesive	
Width	62 mm	

## Conductor and cable markers

Conductor O.D.	6.1 - 13.7 mm	Conductor O.D., max.	13.7 mm
Conductor O.D., min.	6.1 mm	Conductor cross-section, max.	150 mm <sup>2</sup>
Conductor cross-section, min.	0.75 mm <sup>2</sup>	Cross-section for connected wire	0.75 - 150 mm <sup>2</sup>
Halogen	No	Text field height	19.05 mm
Text field width	24.5 mm		

## Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

## Environmental Product Compliance

REACH SVHC	/
------------	---


## Approvals

ROHS	Conform
------	---------

## Technical data

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>



**THM WO 24.5/62 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

Type	RIBBON MM 110/360 SW	Version
Order No.	<a href="#">2005070000</a>	Ink ribbon
GTIN (EAN)	4050118390049	
Qty.	1 pc(s).	