

SAIBM-8/11S-M12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

General ordering data

Version	Field attachable connector, M12, Female socket, straight
Order No.	1118920000
Type	SAIBM-8/11S-M12
GTIN (EAN)	4032248899838
Qty.	1 pc(s).

SAIBM-8/11S-M12

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	58 g
------------	------

Technical data customisable plug-in connectors

Cable diameter	4...6 mm (PG7), 6...8 mm (PG9), 8...10 mm (PG11)	Cable diameter, max.	10 mm
Cable diameter, min.	8 mm	Coding	A-coded
Conductor cross-section, max.	0.5 mm ²	Conductor cross-section, min.	0.14 mm ²
Contact surface	Gold-plated	Housing main material	CuZn
Insulation strength	10 ⁸ Ω	Number of poles	8
Plugging cycles	≥ 100	Pollution severity	3
Protection degree	IP67	Rated current	2 A
Rated voltage	60 V	Shield connection	Yes
Temperature range of housing	-40 ... +85 °C	Threaded ring material	Diecast zinc
Type of connection	Screw connection		

General Info

Number of poles	8	Connection 1	M12
Connection 2	Screw	Housing main material	CuZn
Connection thread	M12	Contact surface	Gold-plated
Protection degree	IP67	Plugging cycles	≥ 100

Standards

Connector standard	IEC 61076-2-101
--------------------	-----------------

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ECLASS 9.0	27-44-01-02	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-02	ECLASS 11.0	27-44-01-02
ECLASS 12.0	27-44-01-16	ECLASS 13.0	27-44-01-02
ECLASS 14.0	27-44-01-16		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E307231

Creation date August 29, 2024 9:04:26 PM CEST

Catalogue status 17.08.2024 / We reserve the right to make technical changes.

SAIBM-8/11S-M12

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

SAIBM-8/11S-M12

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Pole scheme

