

THM GEW FLAG 54/8 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system M-Print® PRO under Windows optimise all labelling efforts.

- High-quality polyester labels in different colours
- Due to their flexible material and the thick adhesive layer, the THM GEW can be used on angled or round objects such as cables or hoses
- Roll-packaged THM ET S7 can be used to label the Simatic 200S, S7-300 and S7-400 modules from Siemens
- Labels are automatically positioned in the printer for perfectly centred prints on each label.
- Labelling with the THM MultiMark or THM MultiMark Plus thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 1 - 12 mm, 54 x 8 mm, white
Order No.	1107350000
Type	THM GEW FLAG 54/8 WS
GTIN (EAN)	4032248882885
Qty.	1 pc(s).

THM GEW FLAG 54/8 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	54 mm	Height (inches)	2.126 inch
Width	8 mm	Width (inches)	0.315 inch
Net weight	673 g		

Temperatures

Operating temperature range	-29...80 °C
-----------------------------	-------------

General data

Adhesive	Natural rubber adhesive		
Colour	white		
Material	Vinyl-coated cotton fabric		
Material colour according to resistance code	9		
Number of markers per combination	1 Reel = 4000 Conductor and cable markers		
Number of markers per packaging unit	Number of markers per combination		4,000
	Form of supply		Reel
	Number of combinations per packaging unit		1
Number of markers per packaging unit	4,000		
Number per roll	4,000		
Operating temperature range	-29...80 °C		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-29 °C		
Printing method	Thermal transfer		
Size of labelling field	21.4 x 8 mm		
UL 94 flammability rating	V-0		
Width	8 mm		

Conductor and cable markers

Conductor O.D.	1 - 12 mm	Conductor O.D., max.	12 mm
Conductor O.D., min.	1 mm	Conductor cross-section, max.	70 mm ²
Conductor cross-section, min.	0.75 mm ²	Cross-section for connected wire	0.75 - 70 mm ²
Text field height	8 mm	Text field width	21.34 mm

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

THM GEW FLAG 54/8 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
Catalogues	Catalogues in PDF-format

THM GEW FLAG 54/8 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

