

**PS\_ZQV\_SET****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

**General ordering data**

Version	Test adapter (terminal), 1000 V, 20 A
Order No.	<a href="#">1116710000</a>
Type	PS_ZQV_SET
GTIN (EAN)	4032248911455
Qty.	1 pc(s).

**PS\_ZQV\_SET****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Height	94 mm	Height (inches)	3.701 inch
Diameter	4 mm	Net weight	82 g

**System specifications**

Version	Test plug
---------	-----------

**Additional technical data**

Type of mounting	Plugged	With snap-in pegs	No
------------------	---------	-------------------	----

**Conductors for clamping (rated connection)**

Type of connection	Plug-in connection
--------------------	--------------------

**Dimensions**

Diameter	4 mm	Pitch in mm (P)	5.4 mm
----------	------	-----------------	--------

**General**

Number of poles	1
-----------------	---

**Rating data**

Rated voltage	1,000 V	Max. voltage of clamp support & plug-gable system	1,000 V
Rated current	20 A	Current at maximum wires	20 A

**Classifications**

ETIM 6.0	EC002555	ETIM 7.0	EC002555
ETIM 8.0	EC002555	ETIM 9.0	EC002555
ECLASS 9.0	27-14-11-48	ECLASS 9.1	27-14-11-48
ECLASS 10.0	27-14-11-48	ECLASS 11.0	27-14-11-48
ECLASS 12.0	27-14-11-48	ECLASS 13.0	27-25-03-04

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	8d191f1d-272c-40a1-8319-7de6fe5d9746

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">Beipackzettel PS_ZQV.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	