

RS D8-U \pm 10V**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Do not use product for new
developments, Only re-
maining stock available



D/A converters convert digital signals into analogue signals.

They are used for converting 8-bit digital signals into standardised analogue current and voltage signals.

D/A converters are very well suited for use in monitoring processes.

General ordering data

Version	DA converter, Input : 8-bit pulse, Output : -10...0...+10 V
Order No.	1123361001
Type	RS D8-U \pm 10V
GTIN (EAN)	4032248103911
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2022-06-30

RS D8-U +-10V

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	72 mm	Height (inches)	2.835 inch
Width	35 mm	Width (inches)	1.378 inch
Length	70 mm	Length (inches)	2.756 inch
Net weight	74 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	0 °C...50 °C
---------------------	----------------	-----------------------	--------------

Input

Input resistance, voltage	50 kΩ per input	Number of inputs	8-bit (1-bit signed)
Rated input level	5...24 V DC = High, 0 V DC = Low, max. 30 V = High		

Output

Conversion time	≤ 30 μs	Number of outputs	1
Offset voltage	≤ 20 mV	Output current	≤ 10 mA max. current
Output voltage, note	-10...+10 V	load impedance voltage	≥ 1 kΩ

General data

Accuracy	± 1 LSB	Configuration	none
Current consumption	25 mA (plus output current)	Galvanic isolation	Without isolation
Protection degree	IP00	Rail	TS 35, TS 32
Voltage supply	24 V DC		

Insulation coordination

EMC standards	EN 61000-6	Galvanic isolation	Without isolation
---------------	------------	--------------------	-------------------

Connection data

Type of connection	Screw connection	Clamping range, rated connection	4 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	4 mm ²

Classifications

ETIM 6.0	EC002653	ETIM 7.0	EC002653
ETIM 8.0	EC002653	ETIM 9.0	EC002653
ECLASS 9.0	27-21-01-20	ECLASS 9.1	27-21-01-90
ECLASS 10.0	27-21-01-20	ECLASS 11.0	27-21-01-20
ECLASS 12.0	27-21-01-20	ECLASS 13.0	27-21-01-20

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	7b5ffb72-271d-4c73-8b09-bd0aaee3697a

RS D8-U +-10V

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity

[Application notes – Declaration of Conformity](#)

User Documentation

[Device description – IS RS 8BIT ADC DAC](#)

[Instruction sheet](#)

Catalogues

[Catalogues in PDF-format](#)

RS D8-U $\pm 10V$

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Electric symbol

