

IE-C5ES8UG0008M40M40-G**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Assembled cables, patch cable Cabinet Line, Cat. 5, PUR,
green

General ordering data

| | |
|------------|----------------------------|
| | |
| Order No. | 1166000008 |
| Type | IE-C5ES8UG0008M40M40-G |
| GTIN (EAN) | 4064675669906 |
| Qty. | 1 pc(s). |

IE-C5ES8UG0008M40M40-G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|-------|-----------------|-------------|
| Length | 0.8 m | Length (inches) | 31.496 inch |
| Net weight | 49 g | | |

Temperatures

| | |
|--------------------------|----------------|
| Installation temperature | -10 °C...60 °C |
|--------------------------|----------------|

Electrical properties

| | |
|------------|----------------------------|
| PoE / PoE+ | conforming to IEEE 802.3at |
|------------|----------------------------|

General standards

| | |
|--------------------|-----------------|
| Connector standard | IEC 60603-7-5 1 |
|--------------------|-----------------|

Standards

| | |
|--------------------|-----------------|
| Connector standard | IEC 60603-7-5 1 |
|--------------------|-----------------|

Cable structure

| | | |
|---------------------------|---|--|
| Arrangement of wire cores | Colour sequence or wires - wire pairs | white/blue - blue, white/ orange - orange, white/ green - green, white/ brown - brown |
| Complete shielding | Twisted pair Shielding braid made from copper wiring | Cross-section 4*2*AWG 26/7 - 4*2*0.128 mm ² |
| Insulation | PE | Insulation cross-section 0.98 mm |
| Material sheath | PUR | Number of wires 8 |
| Sheath diameter, max. | 6 mm | Sheath diameter, min. 5.6 mm |
| Sheathing colour | green | Shielding SF/UTP |
| Strands | 7 | Wire material Stranded tin-plated copper wire |
| Wire pair shielding | Aluminium foil | |

Electrical properties of cable

| | | | |
|-------------------|----------------------------|--------------------------------|-----------------|
| Category | Cat.5 (ISO/IEC 11801) | Test voltage: wire-wire-shield | 750 V DC, 1 min |
| Transmission rate | 10/100 MBit/s, 1000 MBit/s | | |

Mechanical and material properties of cable

| | | | |
|--------------------------------|--------------------|---------------------------------|--|
| Abrasion resistance | very good | Halogen | halogen-free, according to IEC 60754-2 |
| Min. bending radius, once only | 5 x cable diameter | Min. bending radius, repetitive | 10 x cable diameter |
| Resistance to oils | EN 50305 | Resistance to spread of flame | in accordance with IEC 60332-1 |
| Silicone-free | Yes | UV-resistant | Yes |

Plug

| | | | |
|-----------|---|------------|---|
| Plug left | RJ45, IP20, male contact, straight, plug, Plastic, shielded | Plug right | RJ45, IP20, male contact, straight, plug, Plastic, shielded |
|-----------|---|------------|---|

Creation date July 3, 2024 9:33:14 AM CEST

Catalogue status 29.06.2024 / We reserve the right to make technical changes.

IE-C5ES8UG0008M40M40-G**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Plug, left**

Plug left

RJ45, IP20, male contact, straight, plug, Plastic, shielded

Plug, right

Plug right

RJ45, IP20, male contact, straight, plug, Plastic, shielded

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002599 | ETIM 7.0 | EC002599 |
| ETIM 8.0 | EC002599 | ETIM 9.0 | EC002599 |
| ECLASS 9.0 | 27-06-03-08 | ECLASS 9.1 | 27-06-03-08 |
| ECLASS 10.0 | 27-06-03-08 | ECLASS 11.0 | 27-06-03-08 |
| ECLASS 12.0 | 27-06-03-08 | ECLASS 13.0 | 27-06-03-08 |

Approvals

Approvals



ROHS

Conform

Downloads

Catalogues

[Catalogues in PDF-format](#)

IE-C5ES8UG0008M40M40-G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Wiring

| | | | | |
|------|---|---------------|---|------|
| RJ45 | 1 | white, orange | 1 | RJ45 |
| | 2 | orange | 2 | |
| | 3 | white, green | 3 | |
| | 4 | blue | 4 | |
| | 5 | white, blue | 5 | |
| | 6 | green | 6 | |
| | 7 | white, brown | 7 | |
| | 8 | brown | 8 | |

IE-C5ES8UG0008M40M40-G**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Blank**

TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | TM-I 18 MC NE WS | Version |
| Order No. | 1718431044 | TM-I, Insert markers, 18 x 4 mm, white |
| GTIN (EAN) | 4008190349011 | |
| Qty. | 320 pc(s). | |

IE-C5ES8UG0008M40M40-G**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Blank**

TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | TM-I 12 MC NE WS | Version |
| Order No. | 1718411044 | TM-I, Insert markers, 12 x 4 mm, white |
| GTIN (EAN) | 4008190348977 | |
| Qty. | 320 pc(s). | |