

A2LCS/25/NPT3/4-M25F-WM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

A2LC type cable glands are suitable for un-armored cable and provide a conduit connection female thread, maintains flameproof Ex d and Increased Safety Ex e explosion protection.

General ordering data

| | |
|-----------------|--|
| Version | A2LC (Klippon unarmored with conduit connection thread, Ex e/d cable gland), Cable glands, straight, 3/4" NPT, 13.9 mm, OD min. 13.5 - OD max. 20 mm, Stainless steel 1.4404 |
| Order No. | 1187490000 |
| Type | A2LCS/25/NPT3/4-M25F-WM |
| GTIN (EAN) | 4050118081381 |
| Qty. | 12 pc(s). |
| Delivery status | This article will no longer be available in the future. |
| Available until | 2024-08-31 |

Creation date October 4, 2024 8:05:33 PM CEST

Catalogue status 28.09.2024 / We reserve the right to make technical changes.

A2LCS/25/NPT3/4-M25F-WM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Height | 53.8 mm | Height (inches) | 2.118 inch |
| Width | 39.5 mm | Width (inches) | 1.555 inch |
| Length | 69.8 mm | Length (inches) | 2.748 inch |
| Net weight | 248 g | | |

Temperatures

| | |
|-----------------------|-----------------|
| Operating temperature | -50 °C...120 °C |
|-----------------------|-----------------|

Certificate numbers cable gland

| | | | |
|-----------------------------------|---|-------------------------------------|--------------------|
| Certificate No. (IECEX) | IECEXTPS16.0004X | Certificate no. cable gland (ATEX) | TÜV IT 16ATEX 059X |
| Certificate no. cable gland (CCC) | 2020322313000069 | Certificate no. cable gland (IECEX) | IECEX TPS 16.0004X |
| Identification | II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da | | |

General information

| | | | |
|-----------------------------------|---|-----------------------------------|---------------------------|
| AF size 1 | 36 mm | AF size 2 | 36 mm |
| Cable glands | NPT 3/4" | Conduit thread size (metric) | M25 |
| Explosion protection type | Ex d - flameproof, Ex e - increased safety | External thread | 3/4" NPT |
| Halogen | No | Installation guidelines | See assembly instructions |
| Length of thread | 13.9 mm | Material | Stainless steel 1.4404 |
| O-Ring | Silicone | Operating temperature range, max. | 120 °C |
| Operating temperature range, min. | -50 °C | Outer cable diameter, max. | 20 mm |
| Outer cable diameter, min. | 13.5 mm | Pitch of thread | 1.81 mm |
| Protection degree | IP66, IP68 | Seal insert | Silicone |
| Sealing | Silicone | Silicone | Yes |
| Standards | EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7 | Tightening torque | 45 Nm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000441 | ETIM 7.0 | EC000441 |
| ETIM 8.0 | EC000441 | ETIM 9.0 | EC000441 |
| ECLASS 9.0 | 27-14-44-32 | ECLASS 9.1 | 27-14-44-34 |
| ECLASS 10.0 | 27-14-44-32 | ECLASS 11.0 | 27-14-44-32 |
| ECLASS 12.0 | 27-14-08-04 | ECLASS 13.0 | 27-14-08-04 |
| ECLASS 14.0 | 27-14-08-04 | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

A2LCS/25/NPT3/4-M25F-WM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



ROHS

Conform

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | ATEX certification IEC Ex certification CCC approval of Cable glands CE Declaration of conformity |
| Engineering Data | CAD data – STEP |
| User Documentation | Notice of installation |
| Catalogues | Catalogues in PDF-format |