

VP M32-EX W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VP series stopping plugs provide a method of filling unused entries in Ex equipment while maintaining Flame-proof Ex d and Increased Safety Ex e explosion protection and IP66/67/68 ingress rate.

General ordering data

Version	VP (Klippon Ex blanking plug with mushroom head), Blanking plug, straight, M 32 x 1.5, 16 mm, Brass, nickel-plated
Order No.	1188500000
Type	VP M32-EX W
GTIN (EAN)	4050118075373
Qty.	12 pc(s).

VP M32-EX W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	21.5 mm	Height (inches)	0.846 inch
Width	40 mm	Width (inches)	1.575 inch
Length	21.5 mm	Length (inches)	0.846 inch
Diameter	32 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	15 mm	Net weight	149 g

Temperatures

Operating temperature	-50 °C... 120 °C
-----------------------	------------------

Certificate numbers cable gland

Certificate No. (IECEX)	IECEXTPS16.0004X	Certificate no. cable gland (ATEX)	TÜV IT 16ATEX 059X
Certificate no. cable gland (CCC)	2020322313000069	Certificate no. cable gland (IECEX)	IECEX TPS 16.0004X
Identification	II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da		

General information

Cable glands	M 32	Diameter of sealing ring	32 mm
Explosion protection type	Ex d - flameproof, Ex e - increased safety	External thread	M 32 x 1.5
Halogen	halogen-free	Impact resistance	7.00 J
Installation guidelines	See assembly instructions	Length of thread	16 mm
Material	Brass, nickel-plated	O-Ring	Silicone
Pitch of thread	1.5 mm	Protection degree	IP66, IP68
Silicone		Standards	EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7
	Yes		
Tightening torque	65 Nm		

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ETIM 9.0	EC000451
ECLASS 9.0	27-14-44-25	ECLASS 9.1	27-14-44-35
ECLASS 10.0	27-14-44-25	ECLASS 11.0	27-14-44-25
ECLASS 12.0	27-14-08-05	ECLASS 13.0	27-14-08-05

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	0c0edf9f-b35a-4d1f-b8f0-99d4b22ac203

VP M32-EX W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	ATEX certification IEC Ex certification CCC approval of Cable glands CE Declaration of conformity CE Declaration of conformity
Engineering Data	CAD data – STEP
User Documentation	Notice of installation
Catalogues	Catalogues in PDF-format

VP M32-EX W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Brass lock nuts, nickel-plated**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M32 MS	Version
Order No.	1737020000	SKMU MS (brass locknut), Locknut, M 32, 4 mm, Brass, nickel-plated
GTIN (EAN)	4008190956493	
Qty.	100 pc(s).	

Stainless Steel lock nuts, natural finish

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMUS M32-W	Version
Order No.	1185710000	SKMU SS (stainless steel locknut), Locknut, M 32, 3.8 mm, Stainless
GTIN (EAN)	4050118233759	steel 1.4404
Qty.	144 pc(s).	