

**KTB FS 987420 S4E1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Abbildung ähnlich

The Klippon® TB enclosure range provides excellent performance characteristics, even under the most difficult environmental conditions. In addition, it complies with the stricter requirements of potentially explosive atmospheres found in process or power generation industries. The Klippon® TB FS enclosure range offers further improvements to a product line that is already successfully leading the market.

The Klippon® TB FS enclosure range features the following advantages:

- Available in 12 sizes and 3 standard depths
- Equipped with up to 4 gland plates
- The gasket is protected against compression
- Cover lock outside the sealed zone
- Improved temperature performance
- IP66/IP67 protection
- Earthing stud in the cover and base of the enclosure
- Welded mounting feet

**General ordering data**

Version	Klippon TB FS (Terminal Box - Fixing Screw), Empty enclosure, stainless steel enclosure, Height: 980 mm, Width: 740 mm, Depth: 200 mm, Gland plates: Bottom, Material: Stainless steel 1.4404 (316L), electropolished, silver
Order No.	<a href="#">1196710000</a>
Type	KTB FS 987420 S4E1
GTIN (EAN)	4032248979233
Qty.	1 pc(s).

**KTB FS 987420 S4E1**
**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)
**Technical data**
**Dimensions and weights**

Depth	200 mm	Depth (inches)	7.874 inch
Height	980 mm	Height (inches)	38.583 inch
Width	740 mm	Width (inches)	29.134 inch
Mounting dimension - height	625 mm	Mounting dimension - width	766 mm
Net weight	31,320 g		

**Temperatures**

Operating temperature	Note: room temperature (service)	Limited to IP66 protection when used in temperatures greater than 105 °C.
-60 °C...135 °C		

**Cable glands, left**

M12	126	M16	84
M20	54	M25	48
M32	26	M40	22
M50	10	M63	8
M75	6		

**Cable glands, right**

M12	126	M16	84
M20	54	M25	48
M32	26	M40	22
M50	10	M63	8
M75	6		

**Cable glands, top/bottom**

M12	96	M16	64
M20	42	M25	36
M32	20	M40	16
M50	6	M63	6
M75	4		

**Certificate numbers enclosure**

Approval conditions	ATEX, CCoE, DNV, IECEx, INMETRO, KC, NEPSI, CCC, UL AEx Class Div., UL AEx Class Zone, cULus	Attestation of Conformity No. (AoC)	
Certificate No. (ATEX)	KEMA10ATEX0046U	Certificate No. (DNV)	TAE000013S
Certificate No. (IECEX)	IECEXKEM10.0015U	Certificate No. Electronic Box (NEPSI)	2020322303003289
Certificate No. UL 508A	E223801	Certificate No. UL Haz.Loc.	E223792
Certificate No. UL Ord.Loc.	E243298	Certificate No. UL Terminal Box	E223792
Certificate no. (INMETRO)	IEX13.0006U	Certificate no. (cULus)	E256877
Certificate no. Terminal Box (AEx)	E223792	Certificate no. Terminal Box (ATEX)	IBExU14ATEX1050
Certificate no. Terminal Box (IECEX)	IECEXIBE14.0013	Certificate no. Terminal Box (INMETRO)	LMP 21.0017
Certificate no. Terminal Box (KOSHA)	16-AV4BO-0245X	Certificate no. empty enclosure (ATEX)	IBExU14ATEX1028 U
Certificate no. empty enclosure (ECAS)	<b>21-09-25241/ E21-09-053807</b>	Certificate no. empty enclosure (IECEX)	IECEX IBE 14.0004U
Certificate no. empty enclosure (INMETRO)	LMP 21.0016U	Declaration of Conformity No. (DoC LVD)	DE PS261X 160412 001ISS02

**KTB FS 987420 S4E1**
**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)
**Technical data**
**General information**

AF size	10 mm	Access opening: height	928 mm
Access opening: width		Areas of use	Explosive risk zone, Process industry, Oil and gas industry, Chemical industry, Offshore, Onshore
	688 mm		
Dimension of box		Enclosure attachment	4 welded-on mounting feet with 11 mm holes (2 slotted feet and 2 cross-shaped feet)
	925x1130x240		
Flange plate		Flange plate mounting	M6 hexagonal head screws 10 SW
	Yes		
Gland plates		Impact resistance	7 J ATEX version, 10 J version standard
	Bottom		
Integral fixing	4, 6 or 9 stud bolts M6 inner (female) thread	Lid attachment	M6 hex-head slotted screws SW10
Material	Stainless steel 1.4404 (316L)	Material thickness of cover	1.5 mm
Material thickness of enclosure	1.5 mm	Material thickness of flange	3 mm
Max. payload		Note: protection class	If used in temperature ranges above 105 °C, IP protection is limited to IP 66.
	290 kg		
Number of lid screws	10	Operating temperature, max.	135 °C
Operating temperature, min.	-60 °C	Overall dimensions	991 x 791 x 208.5
Position PE bolts	Enclosure side C	Protection class (UL)	Type 3, Type 4X, Type 12
Protection degree	IP66, IP67	Seal material	Silicone
Standards	DIN EN 62208 - Empty enclosure standard, DIN EN 15085-2, EN 60079-0, EN 60079-7, EN 60079-31, IEC 60079-0, IEC 60079-7, IEC 60079-31	Surface finish	
			electropolished
Torque for lid screws	2.5 Nm		

**Housing earth**

Earth, enclosure, internal	Welded-on M6 stainless-steel earth stud in enclosure body and lid., Continuous M10 earth stud in body enclosure
----------------------------	---

**horizontal assembly**

WDU 10 / ZDU 10	6x64	WDU 16 / ZDU 16	5x54
WDU 2,5 / ZDU 2,5 / IDU 2,5	9x127	WDU 35 / ZDU 35	4x40
WDU 4 / ZDU 4	8x106	WDU 6 / ZDU 6	7x80

**vertical assembly**

WDU 10 / ZDU 10	4x88	WDU 16 / ZDU 16	4x74
WDU 2,5 / ZDU 2,5 / IDU 2,5	6x174	WDU 35 / ZDU 35	3x55
WDU 4 / ZDU 4	6x146	WDU 6 / ZDU 6	5x110

**KTB FS 987420 S4E1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Classifications**

ETIM 6.0	EC002503	ETIM 7.0	EC002503
ETIM 8.0	EC002503	ETIM 9.0	EC002503
ECLASS 9.0	27-18-05-02	ECLASS 9.1	27-18-05-02
ECLASS 10.0	27-18-05-02	ECLASS 11.0	27-18-05-02
ECLASS 12.0	27-18-05-02	ECLASS 13.0	27-18-05-02

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	8d5fcdfe-c58e-44e1-a6b4-74d2bbccc9dd

**Approvals**

Approvals



UL File Number Search	UL Website
Certificate no. (cULus)	E256877

## KTB FS 987420 S4E1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">CCC 2020322303002358 KTB Assembly Enclosure</a>
	<a href="#">CCC 2020322303002357 KTB Empty Enclosure</a>
	<a href="#">Attestation of Conformity - Klippon TB Empty Enclosures - AoC DE PS261X 160309 001ISS06</a>
	<a href="#">IBEXU14ATEX1028U</a>
	<a href="#">IBEXU14ATEX1050</a>
	<a href="#">IECEXIBE14.0004U</a>
	<a href="#">IECEXIBE14.0013</a>
	<a href="#">TAE000013S</a>
	<a href="#">GYJ14.1310X</a>
	<a href="#">IECEXPTB11.0071</a>
	<a href="#">PTB11ATEX2019</a>
	<a href="#">16-AV4BO-245X</a>
	<a href="#">P4610581_1</a>
	<a href="#">24-01-100099/E24-01-102546/NB10</a>
	<a href="#">LMP 21.0017 - CAIXA DE JUNÇÃO KLIPPON TB - KTB MH QL FS</a>
	<a href="#">CERTIFICADO - LMP 21.0016U KLIPPON TB</a>
	<a href="#">CERTIFICADO LMP 21.0017 KLIPPON TB</a>
	<a href="#">EU Declaration of Conformity - Klippon TB Empty Enclosures - DoC DE PS261X 160412 001ISS03</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Tender specification	<a href="#">Klippon TB FS 987420 S4E1_1196710000_DE</a>
	<a href="#">Klippon TB FS 987420 S4E1_1196710000_EN</a>
	<a href="#">Klippon TB FS 987420 S4E1_1196710000_NL</a>
User Documentation	<a href="#">Assembly guidelines - empty enclosures</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">MB OVERV. PROCESS WD DE</a>
	<a href="#">MB KLIPPON ENCL.TECN EN</a>
	<a href="#">MB PROCESS EN</a>
	<a href="#">FL WIND 2012 EN</a>
	<a href="#">FL APPL PROCESS EN</a>
	<a href="#">FL SHIPBUILDING 2016 EN</a>
	<a href="#">FL RAILWAY 2014 EN</a>
	<a href="#">PI KLIPPON TB MH QL EN</a>

**KTB FS 987420 S4E1**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

## Dimensioned drawing

