

A2LC/63/M63-M63F-WM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

A2LC type cable glands are suitable for un-armored cable and provide a conduit connection female thread, maintains flameproof Ex d and Increased Safety Ex e explosion protection.

General ordering data

Version	A2LC (Klippon unarmored with conduit connection thread, Ex e/d cable gland), Cable glands, straight, M 63 x 1.5, 19 mm, OD min. 49.5 - OD max. 56 mm, Brass, nickel-plated
Order No.	1205180000
Type	A2LC/63/M63-M63F-WM
GTIN (EAN)	4050118074673
Qty.	4 pc(s).

A2LC/63/M63-M63F-WM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Height	59.8 mm	Height (inches)	2.354 inch
Width	88 mm	Width (inches)	3.465 inch
Length	78.8 mm	Length (inches)	3.102 inch
Net weight	980 g		

Temperatures

Operating temperature	-50 °C...120 °C
-----------------------	-----------------

Certificate numbers cable gland

Certificate No. (IECEX)	IECEXTPS16.0004X	Certificate no. cable gland (ATEX)	TÜV IT 16ATEX 059X
Certificate no. cable gland (CCC)	2020322313000069	Certificate no. cable gland (IECEX)	IECEX TPS 16.0004X
Identification	II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da		

General information

AF size 1	80 mm	AF size 2	80 mm
Cable glands	M 63	Conduit thread size (metric)	M63
Explosion protection type	Ex d - flameproof, Ex e - increased safety	External thread	M 63 x 1.5
Halogen	No	Installation guidelines	See assembly instructions
Length of thread	19 mm	Material	Brass, nickel-plated
O-Ring	Silicone	Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C	Outer cable diameter, max.	56 mm
Outer cable diameter, min.	49.5 mm	Pitch of thread	1.5 mm
Protection degree	IP66, IP68	Seal insert	Silicone
Sealing	Silicone	Silicone	Yes
Standards	EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7	Tightening torque	130 Nm

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-34
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-04	ECLASS 13.0	27-14-08-04

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	9706e29a-947e-49f2-a4db-8015ded62160

A2LC/63/M63-M63F-WM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	ATEX certification IEC Ex certification CCC approval of Cable glands CE Declaration of conformity
Engineering Data	CAD data – STEP
User Documentation	Notice of installation
Catalogues	Catalogues in PDF-format

A2LC/63/M63-M63F-WM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Brass lock nuts, nickel-plated**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M63 MS	Version
Order No.	1737050000	SKMU MS (brass locknut), Locknut, M 63, 6 mm, Brass, nickel-plated
GTIN (EAN)	4008190956523	
Qty.	25 pc(s).	

Nylon flat washer - GWDR

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M63-W	Version
Order No.	1185670000	in closed state, M 63, Nylon 6
GTIN (EAN)	4064675423270	
Qty.	10 pc(s).	