

A2LC/32/NPT1-NPT1F-WM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

A2LC type cable glands are suitable for un-armored cable and provide a conduit connection female thread, maintains flameproof Ex d and Increased Safety Ex e explosion protection.

General ordering data

| | |
|------------|--|
| Version | A2LC (Klippon unarmored with conduit connection thread, Ex e/d cable gland), Cable glands, straight, 1" NPT, 17.3 mm, OD min. 19.5 - OD max. 26.3 mm, Brass, nickel-plated |
| Order No. | 1205410000 |
| Type | A2LC/32/NPT1-NPT1F-WM |
| GTIN (EAN) | 4050118078190 |
| Qty. | 12 pc(s). |

Creation date June 6, 2024 9:42:07 PM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

A2LC/32/NPT1-NPT1F-WM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Height | 53.8 mm | Height (inches) | 2.118 inch |
| Width | 46 mm | Width (inches) | 1.811 inch |
| Length | 69.8 mm | Length (inches) | 2.748 inch |
| Net weight | 320 g | | |

Temperatures

| | |
|-----------------------|-----------------|
| Operating temperature | -50 °C...120 °C |
|-----------------------|-----------------|

Certificate numbers cable gland

| | | | |
|-----------------------------------|---|-------------------------------------|--------------------|
| Certificate No. (IECEX) | IECEXTPS16.0004X | Certificate no. cable gland (ATEX) | TÜV IT 16ATEX 059X |
| Certificate no. cable gland (CCC) | 2020322313000069 | Certificate no. cable gland (IECEX) | IECEX TPS 16.0004X |
| Identification | II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da | | |

General information

| | | | |
|-----------------------------------|---|-----------------------------------|---------------------------|
| AF size 1 | 42 mm | AF size 2 | 42 mm |
| Cable glands | NPT 1" | Conduit thread size (Inch) | NPT 1" |
| Explosion protection type | Ex d - flameproof, Ex e - increased safety | External thread | 1" NPT |
| Halogen | No | Installation guidelines | See assembly instructions |
| Length of thread | 17.3 mm | Material | Brass, nickel-plated |
| O-Ring | Silicone | Operating temperature range, max. | 120 °C |
| Operating temperature range, min. | -50 °C | Outer cable diameter, max. | 26.3 mm |
| Outer cable diameter, min. | 19.5 mm | Pitch of thread | 2.21 mm |
| Protection degree | IP66, IP68 | Seal insert | Silicone |
| Sealing | Silicone | Silicone | Yes |
| Standards | EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7 | Tightening torque | 65 Nm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000441 | ETIM 7.0 | EC000441 |
| ETIM 8.0 | EC000441 | ETIM 9.0 | EC000441 |
| ECLASS 9.0 | 27-14-44-32 | ECLASS 9.1 | 27-14-44-34 |
| ECLASS 10.0 | 27-14-44-32 | ECLASS 11.0 | 27-14-44-32 |
| ECLASS 12.0 | 27-14-08-04 | ECLASS 13.0 | 27-14-08-04 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 9706e29a-947e-49f2-a4db-8015ded62160 |

A2LC/32/NPT1-NPT1F-WM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



ROHS

Conform

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | ATEX certification IEC Ex certification CCC approval of Cable glands CE Declaration of conformity |
| Engineering Data | CAD data – STEP |
| User Documentation | Notice of installation |
| Catalogues | Catalogues in PDF-format |