

**ESG 9/17 K MC NE BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Version	ESG, Device markers x 17 mm, PA 66, Colour: blue, Self-adhesive
Order No.	<a href="#">1208960000</a>
Type	ESG 9/17 K MC NE BL
GTIN (EAN)	403224899035 1
Qty.	200 pc(s).
compatible printer	<a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a>

**ESG 9/17 K MC NE BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	0.8 mm	Depth (inches)	0.031 inch
Height	9 mm	Height (inches)	0.354 inch
Width	17 mm	Width (inches)	0.669 inch
Net weight	0.54 g		

**Temperatures**

Operating temperature range	-40...60 °C
-----------------------------	-------------

**General data**

Adhesive	Double-sided adhesive tape	
Application/manufacturer	Self-adhesive	
Colour	blue	
Halogen	No	
Material	PA 66	
Number of markers per combination	1 MultiCard = Device markers	
Number of markers per packaging unit	Form of supply	MultiCard
Number per sheet	40	
Operating temperature range	-40...60 °C	
Operating temperature range, max.	60 °C	
Operating temperature range, min.	-40 °C	
UL 94 flammability rating	V-2	
Version	Self-adhesive	
Width	17 mm	

**Device markers**

Halogen	No
---------	----

**Classifications**

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04
ECLASS 14.0	27-28-11-04		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Product Change Notification	<a href="#">MultiCard Material modification</a> <a href="#">MultiCard Material Modifikation</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

Creation date November 6, 2024 9:13:25 PM CET

Catalogue status 26.10.2024 / We reserve the right to make technical changes.

**ESG 9/17 K MC NE BL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

