

**DRH275048LT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

DRH DC relays (with blow-out magnet)

- 1 NC contact and 1 NO contact
- Optional AC or DC coils
- With test button and Integrated status LED

**General ordering data**

|            |  |
|------------|--|
| Version    | D-SERIES DRW / DRH, Relay 1 NO contact and 1 NC contact with blow-out magnet AgSnO, Rated control voltage: 48 V DC, Continuous current: 16 A, Flat blade connections (4.8 mm x 0.5 mm), Test button available: Yes |
| Order No.  | <a href="#">1220060000</a>   |
| Type       | DRH275048LT  |
| GTIN (EAN) | 4032248998531  |
| Qty.       | 10 pc(s).  |

Creation date June 4, 2024 3:10:40 PM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

**DRH275048LT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 48 mm  | Depth (inches)  | 1.89 inch  |
| Height     | 36 mm  | Height (inches) | 1.417 inch |
| Width      | 36 mm  | Width (inches)  | 1.417 inch |
| Net weight | 85.3 g |                 |            |

**Temperatures**

|                     |   |                       |                |
|---------------------|---|-----------------------|----------------|
| Storage temperature | -40 °C...60 °C                          | Operating temperature | -40 °C...60 °C |
| Humidity            | 5...85 % rel. humidity, no condensation |                       |                |

**Rated data UL**

|                         |         |
|-------------------------|---------|
| Certificate No. (cURus) | E312083 |
|-------------------------|---------|

**Control side**

|                       |         |                  |                        |
|-----------------------|---------|------------------|------------------------|
| Rated control voltage | 48 V DC | Rated current DC | 30 mA                  |
| Power rating          | 1.5 W   | Coil resistance  | 1600 $\Omega \pm 10\%$ |
| Coil tolerance        | 10 %    | Status indicator | Green LED              |

**Load side**

|   |  |   |                                       |
|---|--|---|---------------------------------------|
| Rated switching voltage                 | 250 V AC   | Continuous current                      | 16 A                                  |
| Max. switching frequency at rated load  | 0.1 Hz   | Max. switching voltage, AC              | 400 V                                 |
| Max. switching voltage, DC              | 300 V  | Inrush current                          | 80 A / 50 ms                          |
| AC switching capacity (resistive), max. | 4000 VA  | DC switching capacity (resistive), max. | 660 W @ 220 V                         |
| Switch-on delay                         | < 20 ms  | Switch-off delay                        | < 20 ms                               |
| Contact type                            | 1 NO contact and 1 NC contact with blow-out magnet (AgSnO) | Mechanical service life                 | 10 x 10 <sup>6</sup> switching cycles |
| Min. switching power                    | 100 mA @ 12 V  |   |                                       |

**General data**

|                                      |   |                        |
|--------------------------------------|---|------------------------|
| Test button available                | Yes   |                        |
| Version of test button               | Lockable test button, Momentary test button |                        |
| Mechanical switch position indicator | Yes   |                        |
| Colour                               | Transparent                                 |                        |
| UL94 flammability rating component   | Component                                   | Housing                |
|                                      | UL94 flammability rating                    | V-2                    |
|                                      | Component                                   | Relay baseplate        |
|                                      | UL94 flammability rating                    | V-0                    |
|                                      | Component                                   | Relay status indicator |
|                                      | UL94 flammability rating                    | HB                     |
|                                      | Component                                   | Relay test button      |
|                                      | UL94 flammability rating                    | HB                     |

DRH275048LT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Insulation coordination

|  |                             |   |                             |
|--|-----------------------------|---|-----------------------------|
| Insulation coordination according to             | EN 61810-1:2008             | Rated voltage   | 400 V                       |
| Pollution severity                               | 3                           | Surge voltage category  | III                         |
| Insulating material group                        | IIIa                        | Clearance and creepage distances for control side - load side | ≥ 6,3 mm                    |
| Dielectric strength for control side - load side | 4 kV <sub>eff</sub> / 1 min | Dielectric strength of neighbouring contacts                  | 4 kV <sub>eff</sub> / 1 min |
| Dielectric strength of open contact              | 4 kV <sub>eff</sub> / 1 min | Protection degree   | IP20                        |

### Further details of approvals / standards

|                         |         |
|-------------------------|---------|
| Certificate No. (cURus) | E312083 |
|-------------------------|---------|

### Connection data

|                        |   |
|------------------------|---|
| Wire connection method | Flat blade connections<br>(4.8 mm x 0.5 mm) |
|------------------------|---|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001437    | ETIM 7.0    | EC001437    |
| ETIM 8.0    | EC001437    | ETIM 9.0    | EC001437    |
| ECLASS 9.0  | 27-37-16-01 | ECLASS 9.1  | 27-37-16-01 |
| ECLASS 10.0 | 27-37-16-01 | ECLASS 11.0 | 27-37-16-01 |
| ECLASS 12.0 | 27-37-16-01 | ECLASS 13.0 | 27-37-16-01 |

### Approvals

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate No. (cURus) | E312083    |

### Downloads

|   |   |
|---|---|
| Approval/Certificate/Document of Conformity | <a href="#">EU Konformitätserklärung / EU Declaration of Conformity</a> |
| Engineering Data                            | <a href="#">CAD data – STEP</a>   |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                |
| Brochures                                   |   |

## DRH275048LT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com


## Drawings

## Wiring diagram




View of Pins from below

## Graph


DC load limit curve  
Resistive load

## Graph




Electrical service life

## Graph



DC operational voltage range

## Dimensional drawing



## DRH275048LT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | ESG 9/11 K MC NE WS        | Version  |
| Order No.  | <a href="#">1857440000</a> | ESG, Device markers x 11 mm, PA 66, Colour: white, Self-adhesive |
| GTIN (EAN) | 4032248402731              |  |
| Qty.       | 200 pc(s).                 |  |

## Protection modules



Pluggable protective modules for the D-SERIES relay sockets, with optional protective functions.

- With free-wheeling diode or RC filter

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | RIM 5 6/230VDC             | Version   |
| Order No.  | <a href="#">1174650000</a> | D-SERIES, Free-wheeling diode, Rated control voltage: 6...230 V DC, |
| GTIN (EAN) | 4032248971305              | Plug-in connection  |
| Qty.       | 10 pc(s).                  |   |

**DRH275048LT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Retaining clips**

Retaining clip for D-SERIES DRW/DRH relays

- Metal retaining clip

**General ordering data**

|            |                            |                                    |
|------------|----------------------------|------------------------------------|
| Type       | DRW/DRH CLIP M             | Version                            |
| Order No.  | <a href="#">1220260000</a> | D-SERIES DRW / DRH, Retaining clip |
| GTIN (EAN) | 4032248999576              |                                    |
| Qty.       | 10 pc(s).                  |                                    |

**Test button cover**

Test button cover for the D-SERIES DRW/DRH relays.

**General ordering data**

|            |                            |                                       |
|------------|----------------------------|---------------------------------------|
| Type       | TEST LEVER BLOCK DRH/DRW   | Version                               |
| Order No.  | <a href="#">7760056249</a> | D-SERIES DRW / DRH, Test button cover |
| GTIN (EAN) | 6944169641626              |                                       |
| Qty.       | 10 pc(s).                  |                                       |

DRH275048LT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## ESG 6/17

**Guaranteed long service life: ESG**

The multi-colour and multi-format labels have a strong adhesive layer to ensure the best possible adhesion to the underlying surface. Double laminated polyester makes the basic material very thin and yet extremely tear-resistant.

**Your benefits with MultiMark**

- "Different materials for various requirements"
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

**General ordering data**

|            |                            |                                       |
|------------|----------------------------|---------------------------------------|
| Type       | ESG 6/17 MM WS             | Version                               |
| Order No.  | <a href="#">2005100000</a> | ESG, Device markers, 6 x 17 mm, white |
| GTIN (EAN) | 4050118390728              |                                       |
| Qty.       | 3,000 pc(s).               |                                       |

**Blank, adhesive backing**

SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |                            |   |
|------------|----------------------------|---|
| Type       | SM 18/9.5 K MC NE GE       | Version   |
| Order No.  | <a href="#">1248590000</a> | SwitchMark, Device markers, 9.5 x 18 mm, Siemens 3 SB, yellow |
| GTIN (EAN) | 4050118038958              |   |
| Qty.       | 200 pc(s).                 |   |

|            |                            |   |
|------------|----------------------------|---|
| Type       | SM 18/9.5 K MC NE GR       | Version                                       |
| Order No.  | <a href="#">1248610000</a> | SwitchMark, Device markers, 9.5 x 18 mm, grey |
| GTIN (EAN) | 4050118038675              |   |
| Qty.       | 200 pc(s).                 |   |

## DRH275048LT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |  |
|------------|----------------------------|--|
| Type       | SM 18/9.5 K MC NE WS       | Version  |
| Order No.  | <a href="#">1248580000</a> | SwitchMark, Device markers, 9.5 x 18 mm, white |
| GTIN (EAN) | 4050118038965              |  |
| Qty.       | 200 pc(s).                 |  |

## Sockets



Relay sockets for the D-SERIES DRW/DRH relays

- Up to 3 CO contacts
- Screw connection

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SPW ECO 3CO                | Version   |
| Order No.  | <a href="#">1220250000</a> | D-SERIES DRW / DRH, Relay socket, Number of contacts: 3, CO |
| GTIN (EAN) | 4032248100101              | contact, Continuous current: 16 A, Screw connection         |
| Qty.       | 10 pc(s).                  |   |

## Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | ESG 6/17 K MC NE GE        | Version   |
| Order No.  | <a href="#">1880110000</a> | ESG, Device markers x 17 mm, PA 66, Colour: yellow, Self-adhesive |
| GTIN (EAN) | 4032248478798              |   |
| Qty.       | 200 pc(s).                 |   |



## DRH275048LT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |  |
|------------|----------------------------|--|
| Type       | ESG 6/17 K MC NE WS        | Version  |
| Order No.  | <a href="#">1880120000</a> | ESG, Device markers x 17 mm, PA 66, Colour: white, Self-adhesive |
| GTIN (EAN) | 4032248478804              |  |
| Qty.       | 200 pc(s).                 |  |

## Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | ESG 6/15 K MC NE WS        | Version  |
| Order No.  | <a href="#">1880100000</a> | ESG, Device markers x 15 mm, PA 66, Colour: white, Self-adhesive |
| GTIN (EAN) | 4032248478781              |  |
| Qty.       | 200 pc(s).                 |  |

|            |                            |   |
|------------|----------------------------|---|
| Type       | ESG 6/15 K MC NE GE        | Version   |
| Order No.  | <a href="#">1880130000</a> | ESG, Device markers x 15 mm, PA 66, Colour: yellow, Self-adhesive |
| GTIN (EAN) | 4032248478910              |   |
| Qty.       | 200 pc(s).                 |   |

DRH275048LT

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
[www.weidmueller.com](http://www.weidmueller.com)

Drawings

Miscellaneous



Type codes