

**A2LC/40/NPT1-1/2-NPT1-1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

A2LC type cable glands are suitable for un-armored cable and provide a conduit connection female thread, maintains flameproof Ex d and Increased Safety Ex e explosion protection.

**General ordering data**

Version	A2LC (Klippon unarmored with conduit connection thread, Ex e/d cable gland), Cable glands, straight, 1 1/2" NPT, 18.4 mm, OD min. 25.5 - OD max. 32.2 mm, Brass, nickel-plated
Order No.	<a href="#">1206640000</a>
Type	A2LC/40/NPT1-1/2-NPT1-1
GTIN (EAN)	4050118078602
Qty.	9 pc(s).

Creation date June 7, 2024 2:59:31 AM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

**A2LC/40/NPT1-1/2-NPT1-1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Height	55.8 mm	Height (inches)	2.197 inch
Width	55 mm	Width (inches)	2.165 inch
Length	71.8 mm	Length (inches)	2.827 inch
Net weight	450 g		

**Temperatures**

Operating temperature	-50 °C...120 °C
-----------------------	-----------------

**Certificate numbers cable gland**

Certificate No. (IECEX)	IECEXTPS16.0004X	Certificate no. cable gland (ATEX)	TÜV IT 16ATEX 059X
Certificate no. cable gland (CCC)	2020322313000069	Certificate no. cable gland (IECEX)	IECEX TPS 16.0004X
Identification	II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da		

**General information**

AF size 1	50 mm	AF size 2	50 mm
Cable glands	NPT 1-1/2"	Conduit thread size (Inch)	NPT 1-1/2"
Explosion protection type	Ex d - flameproof, Ex e - increased safety	External thread	1 1/2" NPT
Halogen	No	Installation guidelines	See assembly instructions
Length of thread	18.4 mm	Material	Brass, nickel-plated
O-Ring	Silicone	Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C	Outer cable diameter, max.	32.2 mm
Outer cable diameter, min.	25.5 mm	Pitch of thread	2.21 mm
Protection degree	IP66, IP68	Seal insert	Silicone
Sealing	Silicone	Silicone	Yes
Standards	EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7	Tightening torque	80 Nm

**Classifications**

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-34
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-04	ECLASS 13.0	27-14-08-04

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	9706e29a-947e-49f2-a4db-8015ded62160

**A2LC/40/NPT1-1/2-NPT1-1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

Approvals



ROHS

Conform

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">ATEX certification</a> <a href="#">IEC Ex certification</a> <a href="#">CCC approval of Cable glands</a> <a href="#">CE Declaration of conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Notice of installation</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>