


CP M DM40**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

In many automation applications, power supply systems are required that function reliably even if a power supply unit fails. With our optimally coordinated supplementary modules, a permanent supply concept is created. Weidmüller's diodes and redundancy modules connect two power supplies to each other in order to compensate for the failure of one device. The diode modules allow with 20 A or 40 A output current to the construction of safe power supply systems

General ordering data

Version	Diode module
Order No.	1222220000
Type	CP M DM40
GTIN (EAN)	4050118005455
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2022-10-31
Alternative product	2486100000

CP M DM40

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	150 mm	Depth (inches)	5.905 inch
Height	130 mm	Height (inches)	5.118 inch
Width	60 mm	Width (inches)	2.362 inch
Net weight	867 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-25 °C...70
Humidity	5...95 %, no condensation		

Input

DC input voltage range	18...30 V DC	Input current	2 x 20 A or 1 x 40 A
Rated input voltage	24 V DC	Wire connection method	Screw connection

Output

Continuous output current @ U _{Nominal}	48 A @ 45 °C, 45 A @ 55 °C, 30 A @ 70 °C	Nominal output current for U _{nom}	40 A @ 60 °C
Output current, max.	48 A	Output voltage, note	Voltage input - 0.7 V
Rated output voltage		Switching thresholds	21.6 V DC, relay is on for Power Good, 20.4 V DC, relay is off for Power Fail
	24 V DC ± 1 %	Wire connection method	Screw connection
Voltage monitoring	Yes, In both inputs		

General data

Degree of efficiency	> 97 % @ 24 V Input voltage	Humidity	5...95 %, no condensation
Mounting position, installation notice	Horizontal on TS35 mounting rail. 50 mm of clearance at top & bottom for air circ. Can mount side by side with no space in between.	Protection degree	IP20

EMC / shock / vibration

Interference immunity test acc. to	EN 61000-4-2 (ESD) EN 61000-4-3 and EN 61000-4-8 (fields) EN 61000-4-4 (burst) EN 61000-4-5 (surge) EN 61000-4-6 (conducted)	Noise emission in accordance with	EN55032
Shock resistance IEC 60068-2-27	15 g In all directions	Vibration resistance IEC 60068-2-6	Class B 1 g according to EN 50178

Insulation coordination

Insulation voltage	0.5 kV _{Input / output - Box}	Pollution severity	2
Protection class	III, with no ground connection, for SELV		

Electrical safety (applied standards)

Electrical machine equipment	Acc. to EN60204	For use with electronic equipment	Acc. to EN50178 / VDE0160
------------------------------	-----------------	-----------------------------------	---------------------------

Creation date June 2, 2024 3:46:59 AM CEST

Catalogue status 18.05.2024 / We reserve the right to make technical changes.

CP M DM40

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Connection data (input)

Conductor cross-section, AWG/kcmil ,
max. 6Conductor cross-section, flexible , min. 2.5 mm²Conductor cross-section, rigid , min. 0.5 mm²Wire connection cross section, flexible
(input), max. 10 mm²Conductor cross-section, AWG/kcmil ,
min. 22Conductor cross-section, rigid , max. 16 mm²

Number of terminals 4 (1+, 2+, 1-, 2-)

Connection data (output)

Conductor cross-section, AWG/kcmil ,
max. 6Conductor cross-section, flexible , max. 10 mm²Conductor cross-section, rigid , max. 16 mm²

Number of terminals 4 (3 +, 4 +, 3 -, 4 -)

Conductor cross-section, AWG/kcmil ,
min. 22Conductor cross-section, flexible , min. 2.5 mm²Conductor cross-section, rigid , min. 0.5 mm²

Signalling

Floating contact Yes

Approbations

Certificate no. (cULus)

E258476

Institute (cULus)

CULUS

Classifications

ETIM 6.0

EC002540

ETIM 7.0

EC002540

ETIM 8.0

EC002540

ETIM 9.0

EC002540

ECLASS 9.0

27-04-07-01

ECLASS 9.1

27-04-07-01

ECLASS 10.0

27-04-07-01

ECLASS 11.0

27-04-07-90

ECLASS 12.0

27-04-07-90

ECLASS 13.0

27-04-07-90

Environmental Product Compliance

REACH SVHC

Lead 7439-92-1

SCIP

c9dca554-f123-4c2f-a680-5a7631aa9527

Approvals

Approvals



ROHS

Conform

UL File Number Search

UL Website

Certificate no. (cULus)

E258476

Downloads

Approval/Certificate/Document of Con- [CP M DM UL 508.pdf](#)
formity [DE_PA5200_160512_001.pdf](#)Engineering Data [CAD data – STEP](#)User Documentation [Operating instructions](#)Catalogues [Catalogues in PDF-format](#)

Brochures

Creation date June 2, 2024 3:46:59 AM CEST

Catalogue status 18.05.2024 / We reserve the right to make technical changes.