

SFX 9/40 S MC NE BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



SlimFix X are halogen-free conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. SlimFix is an acknowledged and approved marker type in traffic engineering. The SF tool allows easy installation even in case of small markers.

- Halogen-free material
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|--------------------|--|
| Version | SlimFix X, Conductor and cable markers, 7 - 40 mm, 40 x 13.62 mm, blue |
| Order No. | 1248790000 |
| Type | SFX 9/40 S MC NE BL |
| GTIN (EAN) | 4050118039221 |
| Qty. | 80 pc(s). |
| compatible printer | 2715590000 2438520000 2438510000 |

SFX 9/40 S MC NE BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Depth | 1 mm | Depth (inches) | 0.039 inch |
| Height | 40 mm | Height (inches) | 1.575 inch |
| Width | 13.62 mm | Width (inches) | 0.536 inch |
| Net weight | 1.5 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

General data

| | | |
|--|---|-----------|
| Colour | blue | |
| Halogen | No | |
| Material | Polyamide 66 | |
| Material colour according to resistance code | 6 | |
| Number of markers per combination | 1 MultiCard = Conductor and cable markers | |
| Number of markers per packaging unit | Form of supply | MultiCard |
| Operating temperature range | -40... 100 °C | |
| Operating temperature range, max. | 100 °C | |
| Operating temperature range, min. | -40 °C | |
| Recommended industries | Transportation, Machinery | |
| Size of labelling field | 40 x 8.5 mm | |
| UL 94 flammability rating | V-2 | |
| Version | Installation with cable ties | |
| Width | 13.62 mm | |

Conductor and cable markers

| | | | |
|-------------------------------|--------------------|----------------------------------|--------------------------|
| Conductor O.D. | 7 - 40 mm | Conductor O.D., max. | 40 mm |
| Conductor O.D., min. | 7 mm | Conductor cross-section, max. | 500 mm ² |
| Conductor cross-section, min. | 16 mm ² | Cross-section for connected wire | 16 - 500 mm ² |
| Halogen | No | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ECLASS 9.0 | 27-40-04-01 | ECLASS 9.1 | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |
| ECLASS 14.0 | 27-28-11-02 | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

SFX 9/40 S MC NE BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

| | |
|-----------------------------|--|
| Engineering Data | CAD data – STEP |
| Product Change Notification | MultiCard Material modification MultiCard Material Modifikation |
| Catalogues | Catalogues in PDF-format |


SFX 9/40 S MC NE BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use



Similar to illustration

