


**WGK 95F VP BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Similar to illustration

The WGK finger-proof-insulated enclosures are especially suitable as industrial electronic enclosures for frequency converters, power supplies or filter components which offer a convenient and reliable form of connection internally and externally. To match the wire guides to the installation requirements in the best possible way, Weidmüller offers two versions with horizontal (WGK) and vertical (WGKV) outlet directions.

**General ordering data**

|              |                                                                                                                                                               |
|--------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version      | OMNIMATE Power - series WGK, Feed-through terminal, Rated cross-section: 95 mm², Screw connection, Wemid (PA), black, Direct mounting, Feed-through (bushing) |
| Order No.    | <a href="#">1250660000</a>                                                                                                                                    |
| Type         | WGK 95F VP BK BX                                                                                                                                              |
| GTIN (EAN)   | 4050118041675                                                                                                                                                 |
| Qty.         | 10 pc(s).                                                                                                                                                     |
| Product data | IEC: 1000 V / 232 A / 35 - 95 mm²<br>UL: 600 V / 230 A / AWG 4 - AWG 4/0                                                                                      |
| Packaging    | Box                                                                                                                                                           |

Creation date May 23, 2024 6:48:46 AM CEST

## WGK 95F VP BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|                          |            |                 |            |
|--------------------------|------------|-----------------|------------|
| Height                   | 74 mm      | Height (inches) | 2.913 inch |
| Height of lowest version | 74 mm      | Width           | 25 mm      |
| Width (inches)           | 0.984 inch | Length          | 49.5 mm    |
| Length (inches)          | 1.949 inch | Net weight      | 182.7 g    |

## System parameters

|                            |                             |                                            |                                   |
|----------------------------|-----------------------------|--------------------------------------------|-----------------------------------|
| Product family             | OMNIMATE Power - series WGK | Wire connection method                     | Cable lug: ring cable / spade lug |
| Conductor outlet direction | 180°                        | Number of poles                            | 1                                 |
| Fitted by customer         | No                          | Tightening torque, min.                    | 15 Nm                             |
| Tightening torque, max.    | 20 Nm                       | Clamping screw                             | M8/Hexagon                        |
| Stripping length           | 27 mm                       | Touch-safe protection acc. to DIN VDE 0470 | IP 20                             |
| Protection degree          | IP20                        |                                            |                                   |

## Material data

|                                       |            |                                       |        |
|---------------------------------------|------------|---------------------------------------|--------|
| Insulating material                   | Wemid (PA) | Colour                                | black  |
| Colour chart (similar)                | RAL 9011   | UL 94 flammability rating             | V-0    |
| Contact material                      | Cu-alloy   | Contact surface                       | tinned |
| Storage temperature, min.             | -40 °C     | Storage temperature, max.             | 70 °C  |
| Operating temperature, min.           | -50 °C     | Operating temperature, max.           | 120 °C |
| Temperature range, installation, min. | -25 °C     | Temperature range, installation, max. | 120 °C |

## Conductors suitable for connection

|                                           |                                                                                                                                                                       |                                           |                    |
|-------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------|--------------------|
| Clamping range, min.                      | 35 mm <sup>2</sup>                                                                                                                                                    | Clamping range, max.                      | 95 mm <sup>2</sup> |
| Wire connection cross section AWG, min.   | AWG 4                                                                                                                                                                 | Wire connection cross section AWG, max.   | AWG 4/0            |
| Solid, min. H05(07) V-U                   | 35 mm <sup>2</sup>                                                                                                                                                    | Solid, max. H05(07) V-U                   | 95 mm <sup>2</sup> |
| Stranded, min. H07V-R                     | 35 mm <sup>2</sup>                                                                                                                                                    | Stranded, max. H07V-R                     | 95 mm <sup>2</sup> |
| Flexible, min. H05(07) V-K                | 35 mm <sup>2</sup>                                                                                                                                                    | Flexible, max. H05(07) V-K                | 95 mm <sup>2</sup> |
| w. wire end ferrule, DIN 46228 pt 1, min. | 35 mm <sup>2</sup>                                                                                                                                                    | w. wire end ferrule, DIN 46228 pt 1, max. | 95 mm <sup>2</sup> |
| Reference text                            | Length of ferrules is to be chosen depending on the product and the rated voltage. The outside diameter of the plastic collar should not be larger than the pitch (P) |                                           |                    |

## Rated data acc. to IEC

|                                                                           |             |                                                                |         |
|---------------------------------------------------------------------------|-------------|----------------------------------------------------------------|---------|
| tested acc. to standard                                                   | IEC 60664-1 | Rated current, min. number of poles (Tu=20°C)                  | 232 A   |
| Rated current, max. number of poles (Tu=20°C)                             | 232 A       | Rated voltage for surge voltage class / pollution degree III/3 | 1,000 V |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 8 kV        |                                                                |         |

## WGK 95F VP BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Rated data acc. to CSA

|                                   |       |                                   |         |
|-----------------------------------|-------|-----------------------------------|---------|
| Rated voltage (Use group B / CSA) | 600 V | Rated voltage (Use group C / CSA) | 600 V   |
| Rated current (Use group B / CSA) | 230 A | Rated current (Use group C / CSA) | 230 A   |
| Wire cross-section, AWG, min.     | AWG 4 | Wire cross-section, AWG, max.     | AWG 4/0 |

## Rated data acc. to UL 1059

Institute (cURus)



Certificate No. (cURus)

E60693

|                                       |       |                                       |         |
|---------------------------------------|-------|---------------------------------------|---------|
| Rated voltage (Use group B / UL 1059) | 600 V | Rated voltage (Use group C / UL 1059) | 600 V   |
| Rated current (Use group B / UL 1059) | 230 A | Rated current (Use group C / UL 1059) | 230 A   |
| Wire cross-section, AWG, min.         | AWG 4 | Wire cross-section, AWG, max.         | AWG 4/0 |

Reference to approval values  
Specifications are maximum values, details - see approval certificate.

## Packing

|           |        |            |        |
|-----------|--------|------------|--------|
| Packaging | Box    | VPE length | 270 mm |
| VPE width | 118 mm | VPE height | 99 mm  |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001283    | ETIM 7.0    | EC001283    |
| ETIM 8.0    | EC001283    | ETIM 9.0    | EC001283    |
| ECLASS 9.0  | 27-14-11-34 | ECLASS 9.1  | 27-14-11-34 |
| ECLASS 10.0 | 27-14-11-34 | ECLASS 11.0 | 27-14-11-34 |
| ECLASS 12.0 | 27-14-11-34 | ECLASS 13.0 | 27-14-11-34 |

## Important note

Notes

- Clearance and creepage distances to other components must be devised in accordance with the relevant application standard. This can be achieved in the device by full encapsulation or by the use of additional spacer plates.
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- Colours: SW = black; GN/YL = green/yellow; GY = grey
- Additional variants on request
- WGK: Rated voltage plastic walls: 1–6 mm = 1000 V; metal walls: < 1 mm = 1000 V; metal walls: 1–3.5 mm = 800 V; metal walls: 3.5–5.5 mm = 690 V
- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

**WGK 95F VP BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

Approvals



ROHS Conform

UL File Number Search UL Website

Certificate No. (cURus) E60693

**Downloads**Approval/Certificate/Document of Con-  
formity[Declaration of the Manufacturer](#)

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL DRIVES EN](#)[MB DEVICE MANUF. EN](#)[FL DRIVES DE](#)[FL BASE STATION EN](#)[FL ELEVATOR EN](#)[FL POWER SUPPLY EN](#)[FL 72H SAMPLE SER EN](#)[PO OMNIMATE EN](#)[PO OMNIMATE EN](#)


## WGK 95F VP BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Dimensional drawing



### Graph



## WGK 95F VP BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Accessories



**Integrate, expand and customise: the perfect supplement to every application.**

Universal system accessories enable easy adaptation of the interfaces to fulfil specific requirements for the relevant application.

## General ordering data

| Type       | DP WGK 95 GY BX            | Version                                            | Product data |
|------------|----------------------------|----------------------------------------------------|--------------|
| Order No.  | <a href="#">1937020000</a> | OMNIMATE Power - series WGK, Feed-through terminal | UL:          |
| GTIN (EAN) | 4032248664801              |                                                    |              |
| Qty.       | 10 pc(s).                  |                                                    |              |
| Type       | DP WGK 95 BK BX            | Version                                            | Product data |
| Order No.  | <a href="#">1250620000</a> | OMNIMATE Power - series WGK, Feed-through terminal | UL:          |
| GTIN (EAN) | 4050118041811              |                                                    |              |
| Qty.       | 10 pc(s).                  |                                                    |              |

## Socket wrench sets

Allen key made from fully hardened, high-alloy chromium-vanadium- steel, acc. to DIN ISO 2936 L (DIN 911), high-quality refined surface.



## General ordering data

| Type       | SK WSD-S 1,5-10,0          | Version       |
|------------|----------------------------|---------------|
| Order No.  | <a href="#">9008850000</a> | Mounting tool |
| GTIN (EAN) | 4032248266609              |               |
| Qty.       | 1 pc(s).                   |               |

**WGK 95F VP BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Blank**

The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |                            |                                                           |
|------------|----------------------------|-----------------------------------------------------------|
| Type       | DEK 5/5 MC NE WS           | Version                                                   |
| Order No.  | <a href="#">1609801044</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397111              | Weidmueller, white                                        |
| Qty.       | 1,000 pc(s).               |                                                           |

**Blank**

The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |                            |                                                           |
|------------|----------------------------|-----------------------------------------------------------|
| Type       | DEK 5/6 MC NE WS           | Version                                                   |
| Order No.  | <a href="#">1609820000</a> | Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 |
| GTIN (EAN) | 4008190203436              | Weidmueller, white                                        |
| Qty.       | 1,000 pc(s).               |                                                           |

**WGK 95F VP BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Blank**

The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |                            |                                                           |
|------------|----------------------------|-----------------------------------------------------------|
| Type       | DEK 5/8 MC NE WS           | Version                                                   |
| Order No.  | <a href="#">1856740000</a> | Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 |
| GTIN (EAN) | 4032248400850              | Weidmueller, white                                        |
| Qty.       | 800 pc(s).                 |                                                           |