


SAIL-M16BW-12-5.0U**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

| | |
|------------|---|
| Version | Sensor/actuator line, One end without connector, M16, Number of poles: 12, 5 m, Socket, angled, Shielded: No, LED: No, Sheath material: PUR, Halogen: Yes |
| Order No. | 1259010500 |
| Type | SAIL-M16BW-12-5.0U |
| GTIN (EAN) | 4050118146745 |
| Qty. | 1 pc(s). |

SAIL-M16BW-12-5.0U**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | |
|------------|-------|
| Net weight | 357 g |
|------------|-------|

Technical specifications for cable

| | | | |
|-------------------------------|----------------------|----------------------------------|--|
| Bending radius, min., moving | 15 x cable diameter | Bending radius, min., stationary | 8 x cable diameter |
| Cable length | 5 m | Colour coding | white, brown, green, yellow, grey, pink, blue, red, black, violet, grey / pink, red / blue |
| Core cross-section | 0.25 mm ² | Halogen | Yes |
| Insulation | PVC | Irradiation crosslinked | No |
| Number of poles | 12 | Outside diameter | 7 mm ± 0.2 mm |
| Resistant to welding beads | No | Sheath material | PUR |
| Sheathing colour | black | Shielded | No |
| Suitable for cable carriers | No | Temperature range, moving | -5...70 °C |
| Temperature range, stationary | -25...70 °C | Torsion resistance | 0 °/m |
| Welding spark resistance | No | | |

General technical data

| | | | |
|------------------------------|----------------|------------------------|----------------------|
| Connection thread | M16 | Contact surface | Gold-plated |
| Housing main material | PUR | Insulation strength | 10 ¹² Ω |
| LED | No | Plugging cycles | ≥ 500 |
| Pollution severity | 1 | Protection degree | IP67 |
| Rated current | 3 A | Rated voltage | 60 V |
| Temperature range of housing | -25 ... +70 °C | Threaded ring material | Brass, nickel-plated |
| Tightening torque | M16: 0.6 Nm | Version | Socket, angled |
| jumpered | No | | |

Electrical properties

| | | | |
|---------------------|--------------------|---------------|------|
| Insulation strength | 10 ¹² Ω | Rated voltage | 60 V |
|---------------------|--------------------|---------------|------|

Plug, left

| | |
|-----------|--|
| Plug left | M16, IP67, female contact, angled 90°, Plastic, unshielded |
|-----------|--|

Plug, right

| | |
|------------|--------------------|
| Plug right | free conductor end |
|------------|--------------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001855 | ETIM 7.0 | EC001855 |
| ETIM 8.0 | EC001855 | ETIM 9.0 | EC001855 |
| ECLASS 9.0 | 27-06-03-11 | ECLASS 9.1 | 27-06-03-11 |
| ECLASS 10.0 | 27-06-03-11 | ECLASS 11.0 | 27-06-03-11 |
| ECLASS 12.0 | 27-06-03-11 | ECLASS 13.0 | 27-06-03-11 |
| ECLASS 14.0 | 27-06-03-11 | | |

SAIL-M16BW-12-5.0U**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

| | |
|--------------------------------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | e8d8af70-4c85-4483-bc8c-9bc5b598e2a9 |
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN |


SAIL-M16BW-12-5.0U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com


Drawings

Dimensioned drawing




Angled socket

Pole scheme



Socket

Wiring diagram



The ideal tool: Screwty[®] with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F