

CC DIA 30/3.5 MC NE WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet CONNECT or Plotter.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

For custom printing: Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	ClipCard, Device markers, 30 x 30 mm, With hole, white
Order No.	1266120000
Type	CC DIA 30/3.5 MC NE WS
GTIN (EAN)	4050118055948
Qty.	60 pc(s).
compatible printer	2715590000 2438520000 2438510000

CC DIA 30/3.5 MC NE WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	1.2 mm	Depth (inches)	0.047 inch
Height	30 mm	Height (inches)	1.181 inch
Width	30 mm	Width (inches)	1.181 inch
Diameter	30 mm	Net weight	2.067 g

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

General data

Application/manufacture	With hole	
Colour	white	
Halogen	No	
Material	Polyamide 66	
Material colour according to resistance code	9	
Number of markers per combination	1 MultiCard = Device markers	
Number of markers per packaging unit	Form of supply	MultiCard
Operating temperature range	-40...100 °C	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Recommended industries	Machinery	
UL 94 flammability rating	V-2	
Version	Ø 30 mm, with 3.5 mm mounting hole	
Width	30 mm	

Device markers

Diameter	30 mm	Drill-hole diameter	3.5 mm
Halogen	No		

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

CC DIA 30/3.5 MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
Product Change Notification	Technical change to MultiCard material - DE Technical change to MultiCard material - EN MultiCard Material modification MultiCard Material Modifikation
Catalogues	Catalogues in PDF-format

CC DIA 30/3.5 MC NE WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Example of use



Similar to illustration

Example of use

