

IE-MC-VLT-1TX-1ST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image**Industrial Fast Ethernet media converter**

- 10/100BaseT(X) auto-negotiation and auto MDI/MDI-X
- Link Fault Pass-Through (LFP)
- Warning in event of power failure and port failure
- Redundant power supply inputs
- -40 to 75 °C operating temperature (T models)
- Designed for explosive-risk areas (Class 1 Div. 2/Atex Zone 2)

General ordering data

Version	Media converter, Fast Ethernet, Number of ports: 1x RJ45, 1 * ST Multi-mode, IP30, -40 °C...75 °C
Order No.	1286890000
Type	IE-MC-VLT-1TX-1ST
GTIN (EAN)	4050118077827
Qty.	1 pc(s).

IE-MC-VLT-1TX-1ST

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	105 mm	Depth (inches)	4.134 inch
Height	135 mm	Height (inches)	5.315 inch
Width	53.6 mm	Width (inches)	2.11 inch
Net weight	630 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...75 °C
Humidity	5 to 95 % (non-condensing)		

EMC conformity and approvals

EMC standards	EN 55032, EN 55024, CISPR 32, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 6 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz bis 1 GHz: 3 V/m, IEC 61000-4-4 EFT: Power: 2 kV; Signal: 2 kV, IEC 61000-4-5 Surge: Power: 1 kV; Signal: 1 kV, IEC 61000-4-6 CS: 3 V/m, IEC 61000-4-8, IEC 61000-4-11	Explosive risk zone	UL/cUL, Class I, Division 2, Groups A, B, C and D, ATEX Zone 2 Ex nA nC IIC T4 Gc
Free fall	According to IEC 60068-2-32	Safety standard	UL508, UL 60950-1, EN 60950-1
Ship use	DNV	Shock	according to IEC 60068-2-27
Vibration	according to IEC 60068-2-6		

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	75 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Fibre optic transceiver characteristics

Transmission rate	100 Mbps		
Transceiver type	Multimode		
Connector type	ST-Duplex		
Transmission distance, typ.	5 km		
Wavelength	typ.	1,300 nm	
	Wavelength	TX	
	min.	1,260 nm	
	max.	1,360 nm	
	Wavelength	RX	
	min.	1,100 nm	
	max.	1,600 nm	
Receive power	min.	-32 dBm	
	max.	-3 dBm	

IE-MC-VLT-1TX-1ST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Transmission power	min.	-20 dBm
	max.	-10 dBm
Link-budget	12 dB	

Guarantee

Time interval	5 years
---------------	---------

Interfaces

Alarm contact	1 relay output with a current capacity of 1 A at 24 V DC	Fibre-optic ports	100BaseFX ports (ST connector), Multimode
Function DIP switch	100BaseFX full-/half-duplex mode, Port surveillance	LED indicator	PWR1, PWR2, FAULT, 10/100M (TP-Port), 100M (fibre-optic port), FDX/ COL (Fibre port)
Number of ports	1x RJ45, 1 * ST Multi-mode	RJ45 ports	10/100BaseT(X)

MTBF

MTBF	According to Standard	MIL-HDBK-217F, GB 25°C
	Operating time (hours), min.	401,000 h

Power supply

Connection type	1 removable 6-pin terminal block		
Current consumption	Voltage	12 V	
	Current	0.32 A	
	Voltage	24 V	
	Current	0.16 A	
Overload current protection	1.1 A		
Reverse polarity protection	Available		
Voltage supply	24 V DC, 2 redundant inputs		
Voltage supply range	Voltage type	DC	
	Voltage, min.	12 V	
	Voltage, max.	45 V	

Technical data

Housing main material	metal	Protection degree	IP30
Speed	Fast Ethernet	Type of mounting	DIN rail, Panel (with optional mounting kit)

Technology

Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X) and 100BaseFX
----------	-------------------------------------------------------------------

IE-MC-VLT-1TX-1ST

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Classifications


ETIM 6.0	EC001467	ETIM 7.0	EC001467
ETIM 8.0	EC001467	ETIM 9.0	EC001467
ECLASS 9.0	19-17-01-14	ECLASS 9.1	19-17-01-14
ECLASS 10.0	19-17-01-32	ECLASS 11.0	19-17-01-32
ECLASS 12.0	19-17-01-32	ECLASS 13.0	19-17-01-14

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b14ea46f-06a9-4191-9f88-14cc6c04a8a8
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197
Certificate no. (cULusEX)	E223527

Downloads

Approval/Certificate/Document of Conformity	DNV certificate ATEX certificate KC certificate EU Declaration of Conformity UK Declaration of Conformity
Engineering Data	CAD data – STEP
User Documentation	Hardware Installation Guide
Catalogues	Catalogues in PDF-format
Brochures	

IE-MC-VLT-1TX-1ST

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Configuration backup and restore module (for use with switches of Value- and PremiumLine such as Basic- and ValueLine WLAN devices)

Module for saving and loading a device configuration

- Reduced system downtime by simple reconfiguration if equipment is swapped over
- Automatic loading of the saved configuration possible after device restart
- Compact and robust design
- Useable with all Weidmüller managed switches and industrial WLAN devices

General ordering data

Type	EBR-MODULE RS232	Version
Order No.	1241430000	Configuration module, IP40, 0 °C...60 °C
GTIN (EAN)	4050118029086	
Qty.	1 pc(s).	

Ethernet


- Suitable for Cat. 5 (up to 100 MHz) and Cat. 6 (up to 250 MHz Class E)
- Suitable for PoE+ (according to IEEE 802.3at, IEEE 802.3bt Type 3 and 4)
- Protection of all wire pairs
- Connection via RJ45 sockets
- Metal housing

General ordering data

Type	VDATA CAT6	Version
Order No.	1348590000	Terminal rail fixing, Surge protection, Cat.6, PoE, 802.3 bt at Type 1,
GTIN (EAN)	4050118153002	802.3 bt at Type 2, 802.3 bt at Type 3, 802.3 bt at Type 4
Qty.	1 pc(s).	

IE-MC-VLT-1TX-1ST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Mounting kit for 19" rack assembly**

- For assembling DIN rail-based devices on 19" racks

**General ordering data**

Type	RM-KIT	Version
Order No.	1241440000	Kit for 19"-rack mounting
GTIN (EAN)	4050118029154	
Qty.	1 pc(s).	