

**KLIPPON POK 252516 EX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

**General ordering data**

Version	Klippon POK (polyester empty enclosure), Empty enclosure, Height: 250 mm, Width: 255 mm, Depth: 160.5 mm, Material: Glass fibre-reinforced polyester, untreated, polished, black
Order No.	<a href="#">1306170000</a>
Type	KLIPPON POK 252516 EX
GTIN (EAN)	4050118108279
Qty.	1 pc(s).
Required tool	<a href="#">9008540000</a>

## KLIPPON POK 252516 EX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	160.5 mm	Depth (inches)	6.319 inch
Height	250 mm	Height (inches)	9.842 inch
Height of lowest version	160.5 mm	Width	255 mm
Width (inches)	10.039 inch	Mounting dimension - height	200 mm
Mounting dimension - width	235 mm	Net weight	3,600 g

## Temperatures

Operating temperature	-55 °C... 100 °C
-----------------------	------------------

## Cable glands, left

M12	32	M16	21
M20	15	M25	8
M32	3	M40	3
M50	2		

## Cable glands, right

M12	32	M16	21
M20	15	M25	8
M32	3	M40	3
M50	2		

## Cable glands, top/bottom

M12	36	M16	32
M20	18	M25	10
M32	8	M40	3
M50	2		

## Certificate numbers enclosure

Approval conditions	ATEX, DNV, IECEX, LR, RMRS, UL AEx Class Div., UL AEx Class Zone, cULus, KC, CCC, INMETRO	Attestation of Conformatiy No. (AoC)	DE PS2600 160308 001ISS01
Certificate No. (ATEX)	IBEXU13ATEX1003U	Certificate No. (DNV)	TAE00002R2
Certificate No. (IECEX)	IECEXIBE13.0004X	Certificate no. (cULus)	E256877
Certificate no. Terminal Box (AEx)	E223792	Certificate no. Terminal Box (ATEX)	IBEXU13ATEX1004 X
Certificate no. Terminal Box (IECEX)	IECEX IBE 13.0004X	Certificate no. Terminal Box (INMETRO)	LMP 21.0021X
Certificate no. Terminal Box (KOSHA)	16-AV4BO-0246X	Certificate no. empty enclosure (AEx)	E223792
Certificate no. empty enclosure (ATEX)	IBEXU13ATEX1003 U	Certificate no. empty enclosure (IECEX)	IECEX IBE 13.0003U
Certificate no. empty enclosure (INMETRO)	LMP 23.0528U	Declaration of Conformatiy No. (DoC LVD)	DE_PS2600_160412_001ISS01

## KLIPPON POK 252516 EX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## General information

Access opening: height	238.02 mm	Access opening: width	243.02 mm
Areas of use	Explosive risk zone, Harbour facilities, Machine construction, Process industry, Transportation	Enclosure attachment	Installation through the housing rear wall, Fixing lugs
Flange plate	No	Impact resistance	7 J ATEX version
Lid	Yes	Lid attachment	Slotted/Phillips screws
Material	Glass fibre-reinforced polyester	Material thickness of cover	5.4 mm
Material thickness of enclosure	5.99 mm	Number of lid screws	4
Operating temperature, max.	100 °C	Operating temperature, min.	-55 °C
Protection class (UL)	Type 4, Type 4X	Protection degree	IP66
Seal material	Silicone	Standards	DIN EN 62208 - Empty enclosure standard, IEC 60079-0, IEC 60079-7, IEC 60079-31
Surface finish	untreated, polished	Torque for lid screws	2.5 Nm
UL 94 flammability rating	V-0		

## horizontal assembly

WDU 10 / ZDU 10	2x19	WDU 16 / ZDU 16	2x15
WDU 2,5 / ZDU 2,5 / IDU 2,5	2x38	WDU 4 / ZDU 4	2x31
WDU 6 / ZDU 6	2x23		

## vertical assembly

WDU 2,5 / ZDU 2,5 / IDU 2,5	*	WDU 4 / ZDU 4	*
-----------------------------	---	---------------	---

## Classifications

ETIM 6.0	EC002503	ETIM 7.0	EC002503
ETIM 8.0	EC002503	ETIM 9.0	EC002503
ECLASS 9.0	27-18-05-02	ECLASS 9.1	27-18-05-02
ECLASS 10.0	27-18-05-02	ECLASS 11.0	27-18-05-02
ECLASS 12.0	27-18-05-02	ECLASS 13.0	27-18-05-02

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	afb385d0-c52b-4449-8502-203596817ab0
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c

## KLIPPON POK 252516 EX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E256877

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">CCC 2020322303002628 POK Assembly Enclosure</a> <a href="#">UKCA TÜV 22 UKEX 7093 X</a> <a href="#">UKCA TÜV 22 UKEX 7092 U</a> <a href="#">Attestation of Conformity - KlippON POK Empty Enclosures - AoC DE PS2600 160308 001ISS03 14 20001</a> <a href="#">TAE00002R2</a> <a href="#">IECEXIBE13.0004X</a> <a href="#">16-AV4BO-246X</a> <a href="#">IBEXU13ATEX1003U</a> <a href="#">IBEXU13ATEX1004X</a> <a href="#">IECEXIBE13.0003U</a> <a href="#">INMETRO CERTIFICADO LMP 21.0021X KLIPPON POK</a> <a href="#">EU Declaration of Conformity - KlippON POK Empty Enclosures Ex - DoC DE PS2600 160412 001ISS02</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Tender specification	<a href="#">KlippON POK 252516 Ex_1306170000_DE</a> <a href="#">KlippON POK 252516 Ex_1306170000_EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">MB OVERV. PROCESS WD DE</a> <a href="#">MB KLIPPON ENCL.TECN EN</a> <a href="#">MB PROCESS EN</a> <a href="#">FL KLIPPON POK EN</a> <a href="#">FL SHIPBUILDING 2016 EN</a> <a href="#">FL SHIPBUILDING 2016 EN</a>

# KLIPPON POK 252516 EX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

